



K-Type Marker

TE Internal #: CY2995-000

K-Type Marker, Pre-Printed Markers, Tie-On, 65 Marker Size,
Compatible Cable Diameter Range 4.2 – 7. mm [.165 – .276 in],
White, Straight Cut

[View on TE.com >](#)

Identification & Labeling > Pre-Printed Markers



Marker Style: **Tie-On**
Marker Size: **65**
Compatible Cable Diameter Range: **4.2 – 7. mm [.165 – .276 in]**
Primary Product Color: **White**
Marker Cut: **Straight**

Features

Body Features

Marker Style	Tie-On
Marker Size	65
Primary Product Color	White
Primary Product Material	Flexible PVC

Dimensions

Compatible Cable Diameter Range	4.2 – 7. mm[.165 – .276 in]
Product Width	6 mm[.23 in]

Printer/Label Features

Marker Cut	Straight
------------	----------

Packaging Features

Packaging Method	Box
Packaging Quantity	100

Other

Printed Marking Color	Black
-----------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-T3437-K1
K-TYPE TIE-ON MARKERS

TE Part # EC6562-000
13611942

TE Part # EC4942-000
11310000

TE Part # EC4943-000
11320000


TE Part # EC4941-000
11300000

Also in the Series | K-Type Marker



Pre-Printed Markers(93)

Customers Also Bought



TE Part #2-1586041-0
20P VAL-U-LOK R/A HDR V2



TE Part #8-215460-6
MICRO-MATCH FSID P



TE Part #1-1393774-7
V23026A1006B201



TE Part #EJ1954-000
Z-TYPE PUSH-ON MARKERS



TE Part #1-1623931-9
CFR25 5% 39R



TE Part #2-1623931-9
CFR25 5% 3R9



TE Part #8-1623931-4
CFR25 5% 8R2



TE Part #2-1393774-0
V23026C1051B201



TE Part #2-2176373-6
RQ 0805 18R2 0.1% 10PPM 1K RL

Documents

Product Drawings

CCK-ERK-3-B

English



TE Part #4-2176373-1
RQ 0805 26R1 0.1% 10PPM 1K RL

Datasheets & Catalog Pages

K-Type Markers

English