

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191390018

Status:

Active

Overview:

Solderless Terminals

Description:

Avikrimp Block Spade Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5), Width 6.22mm

Documents:


Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR18689
UL		E32244
General		
Product Family		Ring and Spade Terminals
Series		19139
Crimp Quality Equipment		Yes
Overview		Solderless Terminals
Product Name		Avikrimp
Type		Spade Block
UPC		800753102620
Physical		
Barrel Type		Closed
Flammability		94V-2
Insulation		Nylon (PA)
Material - Plating Mating		Tin
Net Weight		0.758/g
Packaging Type		Bag
Stud Size		6 (M3.5)
Wire Insulation Diameter		3.56mm
Wire Size AWG		18, 20, 22
Wire Size mm²		0.25-1.50
Electrical		
Voltage - Maximum		600V
Material Info		
Engineering Number		AA-838-06
Reference - Drawing Numbers		
Product Specification		PS-19902-011-001, PS-19902-013-001
Sales Drawing		SD-19139-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2020)9139-DC (19

Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19139 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640010100
Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100

ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 08/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION