


ZH2-15.0-0-FSP-SM

✕ OBSOLETE

TE Internal #: F59466-000

TE Internal Description: ZH2-15.0-0-FSP-SM

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought





TE Part #2333393-3
QSFP28 to QSFP28 Cable Assembly:
30 AWG



TE Part #3-644426-7
Nylon Tin Plated Receptacle: 2.54mm,
No Mating Alignment, MTA 100



TE Part #8-180984-1
FASTON 250 FLAG BOOT HSG
NYLON BLK



TE Part #1060875-2
MCX CABLE PLUG, CRIMP ATTACH



TE Part #1986185-1
Strain Relief, 6 Posn, D5200 Dynamic. 2



TE Part #208810-2
PLUG ASSY, COAX MIX, AMPLIMITE



TE Part #1-2373376-0
10P, 2MM, SHRD HDR, DRV, SMD, 0.1
AU, TB



TE Part #1776695-1
Strain Relief, D5200, Dynamic



TE Part #1986186-1
Strain Relief, 20 Posn, D3000 Dynamic, 2

Documents

Datasheets & Catalog Pages
ZH2 Pages from 9-1773447-9

English

Product Specifications
Quality Specification

English