



Fiber Optics > Fiber Optic Cable Assemblies > Rugged Fiber Cable Assemblies



Cable Assembly Length: 50 m

Features

Product Type Features

MPO Cable Assembly	No
Product Type	Accessory
Fiber Channel	No

Other

Cable Assembly Length	50 m
-----------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 2835205-1
FULLAXS MINI BULKHEAD WITH DP-LC ADAPTOR




TE Part # 2061920-1
FULLPROOF80 MINI FIELD INSTALL KIT



TE Part # 2061981-1

Also in the Series | FullAXS Mini



Rugged Fiber Cable Assemblies(20)

Customers Also Bought



TE Part #1367073-1
SFP Connectors



TE Part #1734037-7
Champ 050 series,68pos,Au over PdNi




TE Part #2227303-1
CAGE ASSEMBLY, SFP, .140 SOLDE




TE Part #1-57051-0
Madison Spec 100-7096 Rev. 3







TE Part #2007868-2
IMP100S,H,V5P16C,UG,OEWS39,4.9




TE Part #2061980-1
FOSM GLARO LEAD 4.8 MM FXS
MINI 1 M




TE Part #2061980-3
FOSM GLARO LEAD 4.8 MM FXS
MINI 3 M



TE Part #YDTS32T23NV0010000
CAP ASSEMBLY



TE Part #2061933-1
FULLPOWER MINI FIELD INSTALL
ASSEMBLY



TE Part #2061953-2
FULLAXS MINI BULKHEAD CAP

Documents

Product Drawings

FULLPROOF140 MINI FIELD INSTALL KIT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2061973-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2061973-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2061973-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Fiber Optic Products_0412

English

FullAXS Brochure (English)

English