

**MOSFET BASED
DC SOLID-STATE RELAY**
(With built-in transient voltage suppressor)

- ▶ Latest MOSFET technology generation.
- ▶ Ultra low on-state resistance.
- ▶ Low output leakage current.
- ▶ Low control current consumption.
- ▶ Built-in overvoltage protection (TVS)
- ▶ Reverse protected triggered control input to avoid linear control risks
- ▶ No radiated or conducted disturbances
- ▶ Touch protected housing IP20






SOM06075



| | |
|-----------------------------------|-----------|
| Control voltage range | 3.5-32VDC |
| Max transient peak voltage | 75v |
| Max. DC Mains peak voltage | 40VDC |
| Max. Load Current (with heatsink) | 60ADC |

| DC Mains voltage range | Load current range | Control input voltage range | In & case / Out Insulation | Connections | Dimensions (WxHxD) | Weight |
|------------------------|---------------------------|-----------------------------|----------------------------|-----------------|--------------------|--------|
| 5-40VDC (75Vpeak) | Up to 60A (with heatsink) | 3.5-32VDC | 2.5kV | Screw terminals | 45 x 58.5 x 30 | 80g |



Proud to serve you

CONTROL INPUT CHARACTERISTICS

| INPUT CIRCUIT | CHARACTERISTIC | LABEL | VALUE | INFO. | Fig. 4 CONTROL CURRENT vs. CONTROL VOLTAGE |
|---------------|------------------------------|----------------------------|--------------------|---------------------------|---|
| | Nom. Control voltage | U_{Cnom} | 12-24VDC | | |
| | Nom. Control current | I_{Cnom} | 35mADC | -100µA/°C | |
| | Control voltage range | U_c | 3.5 – 32VDC | typical=3.3V | |
| | Control current consumption | I_c | 32 – 35mADC | See curve | |
| | Releasing control voltage | U_{Coffmax} | 1VDC | Typical= 2.6V | |
| | Max. reverse control voltage | -U_{Cmax} | 32VDC | -I _{cmax} <100µA | |
| | Input impedance | R_{in} | Current limitation | See curve | |

TIME CHARACTERISTICS

| TIME CHARACT. | CHARACTERISTIC | LABEL | VALUE | <p>For high frequency, take 2 x I_e to calculate the heatsink; the protections must be chosen carefully. Please consult us if any.</p> |
|-----------------------|-----------------------------|--------------|-------|--|
| | Turn on time | ton | 20µs | |
| | Turn on delay | tdon | 20µs | |
| | Turn off time | toff | 20µs | |
| | Turn off delay | tdoff | 20µs | |
| Max. On-Off frequency | F_(on-off) | >1000Hz | | |

POWER OUTPUT CHARACTERISTICS

| POWER CIRCUIT | CHARACTERISTIC | LABEL | VALUE | INFO. |
|---------------|---|--------------------------------------|------------------------------------|---|
| | Nominal voltage | U_{enom} | 24VDC | |
| | Voltage range | U_t U_e | 5-40VDC | U _{tmax} =40VDC |
| | Non-repetitive peak voltage | U_{tp} | 75V | |
| | Overvoltage protection | D1 | 39V (Transient voltage suppressor) | 1500W / 1ms See fig.10 & 11 |
| | Off-state max reverse voltage drop (internal diode) | -U_t | 0.92V | @I _e =75A & @U _c =0 See fig. 6 |
| | Maximum nominal currents | I_{e max} | Resistive 60A | Motor Please contact us |
| | Max. non-repetitive peak current | I_{epeak} | Switch OFF D<1% 294A | Switch OFF F _{max} 60A |
| | | | | ON-state 750A |
| | Min. load current | I_{emin} | 5mA | |
| | Max. leakage current | I_{elk max} | 3mA | @U _{tmax} @T _{jmax} |
| | Max. on-state resistance | R_{Dson} | 4.5mOhms @T _j =25°C | 8.2mOhms @T _j =125°C |
| | Typ. output capacitance | C_{out} | 1.5nF | @U _{tp} |
| | Junction/case thermal resistance per power element | R_{thjc} | 1.2K/W | |
| | Built-in heatsink thermal resistance vertically mounted | R_{thra} | 10K/W | @ΔT _{ra} =75°C |
| | Heatsink thermal time constant | T_{thra} | 10 minutes | @ΔT _{ra} =60°C |
| | Control inputs/power outputs insulation voltage | U_{imp} | 2.5kV | |
| | Inputs/case insulation voltage | U_{imp} | 2.5kV | |
| | Outputs/case insulation voltage | U_{imp} | 2.5kV | |
| | Isolation resistance | R_{io} | 1GΩ | |
| | Isolation capacitance | C_{io} | <8pF | |
| | Maximum junction temperature | T_{jmax} | 175°C | |
| | Storage ambient temperature | T_{stg} | -40->+100°C | |
| | Operating ambient temperature | T_{amb} | -25->+90°C | See fig. 9 |
| | Max. case temperature | T_c | 100°C | |

OUTPUT SWITCH CHARACTERISTIC CURVES

Fig. 5 ON RESISTANCE VS JUNCTION TEMPERATURE




Fig. 6 REVERSE VOLTAGE DROP VS REVERSE CURRENT




Fig. 7 POWER ELEMENT TRANSIENT THERMAL IMPEDANCE vs. PULSE DURATION




Fig. 8 ON-STATE PEAK OVERLOAD CURRENT vs. PULSE DURATION





Fig. 9 POWER DISSIPATED AND LOAD CURRENT LIMIT VS TEMPERATURE




10K/W = No Heatsink / 1LD12020
2.1K/W = WF210000
0.9K/W = WF115100

4K/W = 150x150x3mm aluminium sheet
1.2K/W = WF121000
0.75K/W = WF070000

2.2K/W = WF262100 / WF151200
1.1K/W = WF131100
0.55K/W = WF050000

0.3K/W = WF031100

BUILT-IN OVERVOLTAGE PROTECTION CHARACTERISTICS



GENERAL INFORMATION

| | | | | |
|--------------|--------------------|--|--|--------------------|
| MISC. | Display | | Green LED (indicates relay has switched ON) | |
| | Housing | | UL94V0 | |
| | Mounting | | 2 screws (M4x12mm ; tightening = 1.2N.m) | See mounting sheet |
| | Noise level | | None | |
| | Weight | | 80g | |

STANDARDS

| | | | | |
|----------------|--|--|------------|--|
| GENERAL | Standards | | IEC60947-1 | |
| | Protection level | | IP20 | |
| | Protection against direct touch | | Yes | |
| | CE marking | | Yes | |
| | UL, cULUS | | Yes | |

| E.M.C. IMMUNITY | TYPE OF TEST | STANDARD | LEVEL | EFFECT |
|------------------------|------------------------|--------------|-----------------|--------|
| | Fast transients bursts | EN61000-4-4 | 4kV criterion B | |
| | Electric chocks | EN61000-4-5 | 1kV criterion B | |
| | Voltage drop | EN61000-4-11 | - | |






CONNECTIONS






Direct connection with wires with or without ferrules



With ring terminals



| okpac [®] | | | | Control wiring | |
|---|---|---|---|--|---|
| Number of wires | | | | Screwdriver type | Recommended tightening torque M4 screw |
| 1 | | 2 | | | |
| SOLID (No ferrule) | FINE STRANDED (With ferrule) | SOLID (No ferrule) | FINE STRANDED (With ferrule) |  | N.m |
|  |  |  |  | | |
| 0,75 ... 2,5 mm ² AWG18...AWG14 | 0,75 ... 2,5 mm ² AWG18...AWG14 | 0,75 ... 2,5 mm ² AWG18...AWG14 | 0,75 ... 2,5 mm ² AWG18...AWG14 | POZIDRIV 2 | Mini 1,2 / Typ 1.5 / Max 2 |

| okpac [®] | | | | Power wiring | |
|---|---|---|---|--|---|
| Number of wires | | | | Modèle de tournevis / Screwdriver type | Recommended tightening torque M5 screw |
| 1 | | 2 | | | |
| SOLID (No ferrule) | FINE STRANDED (With ferrule) | SOLID (No ferrule) | FINE STRANDED (With ferrule) |  | N.m |
|  |  |  |  | | |
| 1,5 ... 10 mm ² AWG16...AWG8 | 1,5 ... 6 mm ² AWG16...AWG10 | 1,5 ... 10 mm ² AWG16...AWG8 | 1,5 ... 6 mm ² AWG16...AWG10 | POZIDRIV 2 | Mini 2 / Typ 2.4 / Max 3 |

Power with ring terminals.


W max = 12,6mm

16 mm² (AWG6)

25 mm² (AWG4)

35mm² (AWG2 / AWG3)

50mm² (AWG0 / AWG1)



Suitable ring terminals and special kit for high current can be delivered: see high power SSR and data-sheet for power connection.

IP20 flaps

Flaps are delivered mounted on the relay.

Labels

Marking labels are available, for mounting on flaps.
Part number : 1MZ09000
(delivered per 200 parts)

FASTONS: Consult us




DIMENSIONS AND ACCESSORIES

Fig. 12

DIMENSIONS (mm)

CAD documents : www.celduc-relais.com/uk/plan3D.asp




ACCESSORIES

**READY TO USE OVERVOLTAGE PROTECTION
ESO01000**

(Please check our website for availability)

This device includes a diode (D2) and a capacitor (C1) suitable for most of the DC application.

To be mounted close to the SOM.



Please consult our website for other accessory references
(Heatsinks, mounting adaptors, thermal grease...)