



G06-12-110-3

Semi-Traction Bloc Battery



Electrical Specifications

Voltage	12V
80% DOD Voltage Cutoff	11.2V
Self Discharge	Less than 3% per month (20°C/68°F)
Charge Temperature	Min: -10°C (14°F) / Max: 50°C (122°F)
Discharge Temperature**	Min: -40°C (-40°F) / Max: 50°C (122°F)
Storage	Min: -20°C (-4°F) / Max: 60°C (140°F)

Amp Hours (AH)			
20 HR	10 HR	5 HR	3 HR
120	122	110	103

** CAUTION: Depths of discharge, operating voltages and currents, when designing systems for use at maximum temperatures, will vary.

Mechanical Specifications

Industry Reference	DINA	
Length (A)	20 in	513 mm
Width (B)	7.4 in	189 mm
Height (C)	8.5 in	217 mm
Weight	99 lb	45 kg
Terminal (Opt'l)*	A-POLE	
Cell(s)	6	
Electrolyte	Gel	
Terminal Torque Nm	n/a	

NOTE: There is a tolerance of +/-2%.

Features

- Maintenance-free bloc batteries in Gel technology (no topping up during lifetime)
- Good high current performance for extreme operating conditions
- High-class patented safety valve
- 700 cycles (DIN EN 60254-1) (IEC 254-1)
- Valve-regulated lead-acid battery
- Recyclable
- Long cycle life
- Low self discharge rate allows for up to 2 years shelf life

Classified as a non-spillable battery is not restricted for transportation by:

- Air (IATA/ICAO provision 67)
- Ground (STB, DOT-CFR-HMR49)
- Water (IMDG amendment 27)

Applications


- Electric vehicles
- Wheelchairs
- Cleaning machines
- Electric working platforms
- Universal for multiple cyclic applications

Charging profile


IU Charging I = min. 12% C₅ max. 18% C₅
U = 2.4 V per cell

IUI Charging I₁ = min. 12% C₅ max. 18% C₅
U = 2.35 V per cell
I₂ = 1.5% C₅ for max. 4 hours


Self discharge at different temperatures



Capacity vs. temperature



Storage: Determine the state of charge



Relation between charging, voltage and temperature

