

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008500183

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK Trifurcon Crimp Terminal 7258, 22-26 AWG, Reel, Brass Tin (Sn)

Documents:

Drawing (PDF)

Product Specification PS-40-02-001 (PDF)

Packaging Specification PK-2759-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	7258
Application	Power
Crimp Quality Equipment	Yes
Overview	KK Interconnect Solutions
Packaging Alternative	08500185 (Loose)
Product Name	KK, Trifurcon
UPC	800753614468
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.154/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	7258-(P909)
Reference - Drawing Numbers	
Packaging Specification	PK-2759-002-001
Product Specification	PS-40-02-001
Sales Drawing	SD-7258-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Low-Halogen

Status

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

7258 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	11030016
Terminator Die	11402097
Terminator Die	11402099
PremiumGrade Hand Crimp Tool for KK 3.96mm Terminals, 22-26 AWG	638117400
Mini-Mac Applicator	638881000

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION