

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008560108

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 396 Crimp Terminal 2578, 22-26 AWG, Bag, Brass, 0.51µm Select Gold (Au) over Gold Flash

Documents:

Drawing (PDF)

Product Specification PS-08-50-001 (PDF)

Packaging Specification PK-2759-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	2578
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	KK Interconnect Solutions
Packaging Alternative	08560107 (Reel)
Product Name	KK 396, KK 508
UPC	800753745933
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.150/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.051µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	2578-(550)L
Reference - Drawing Numbers	
Packaging Specification	PK-2759-001-001
Product Specification	PS-08-50-001
Sales Drawing	SD-2578-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2020)9139-DC (19

Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

2578 Series

Use With

2574 , 2139 , 41695 , 3069 , 6422 , 5265 , 5239

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals PremiumGrade Hand Crimp Tool for KK 3.96mm Terminals, 22-26 AWG	11030016638117400

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION