


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0008700001
Status: Active
Description: 4.80mm Pitch Crimp Terminal, Female, Reel

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-5025-002-001 \(PDF\)](#)
[Product Specification PS-5025-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	5005
Application	Power
Crimp Quality Equipment	Yes
Product Name	N/A
UPC	800753614277
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	150.200/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.00mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A
Material Info	
Engineering Number	5005T
Reference - Drawing Numbers	
Crimp Specification	CS-5005~5006-001
Product Specification	PS-5025-001-001, PS-5025-002-001
Sales Drawing	SD-5005X-051



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Low-Halogen	China RoHS
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series
5005 Series

Mates With
5006

Use With
5025 Receptacle

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Terminator Die	11402064
Hand Crimp Tool for Standard 1.57mm Pin and Socket Crimp Terminals, 18-24 AWG	638191300
Mini-Mac Applicator	638936000

Japan

Description	Product #
Applicator for M211A Bench Press, 14-28 AWG Wire	<u>11260034</u>
S-1 Applicator for 4.80mm Pitch Male and Female Crimp Terminals, 18-24 AWG, Wire Insulation Diameter 2.30-3.00mm	<u>2023933700</u>
S-1 Applicator for 4.80mm Pitch Male and Female Crimp Terminals, 18-24 AWG, Wire Insulation Diameter 1.30-2.70mm	<u>2023933710</u>

This document was generated on 08/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION