

10 9 8 7 6 5 4 3 2 1

F


E

D

C


B

A



ITEM	COMPONENT	MATERIAL	FINISH
1	REC SHELL	BRASS	NICKEL PLATED
2	INSERT	PA	BLACK
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	WIRES	COPPER/PVC	NONE
5	O-RING	NBR	BLACK
6	POTTING MATERIAL	WEVO	NONE

COLOR CODE:
1 BROWN
2 WHITE
3 BLUE
4 BLACK



POL	MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH
4	1200845103	WR4J26E03C3003	300 ± 10

VOLTAGE RATING: 250 VAC / VDC
AMPERAGE RATING: 4 A
PROTECTION CLASS: IP 67/68/69K
OPERATING TEMPERATURE: -25°C / 90°C
UL CERTIFICATION: FILE NO. E152210
CSA CERTIFICATIONS: FILE NO. LR6837

ENTER DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
EC NO: IPG2014-0351		DRWN:BBRAUCH 2013/09/25		mm INCH		MM ONLY		2:1	METRIC	THIRD ANGLE PROJECTION	
CH'D:AP0HL 2013/10/16		APPR:CBURGER 2014/01/31		4 PLACES $\pm$ --- $\pm$ ---		DRAWN BY NSTAUDIGEL		DATE 2010/01/28		TITLE REC U12 4P AC MA STR PA	
				3 PLACES $\pm$ --- $\pm$ ---				CHECKED BY		DATE	
				2 PLACES ± 0.05 $\pm$ ---				APPROVED BY		DATE	
				1 PLACE ± 0.3 $\pm$ ---				FPACHER		2010/02/01	
				0 PLACE ± 0.5 $\pm$ ---				MATERIAL NO.		DOCUMENT NO.	
				ANGULAR $\pm 1^\circ$		see table				SD-120084-023	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 1 OF 1	

9 8 7 6 5 4 3 2 1