This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1200878712

Status: Active

Overview: Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable

Description: Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 4 Poles, Female (Straight) to Male (Straight), 24 AWG, WSOR Cable, 3.0m (9.84') Length



Series image - Reference only

Documents:

Drawing (PDF) | RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	120087
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Nano-Change (M8)
Region	Europe
Type	Double Ended
UPC	889056073981
Physical	
Cable Diameter	4.80mm (.189")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	98.544/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25°C to +85°C
Wire Size AWG	24
Wire/Cable Type	WSOR
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	30V
Material Info	
Engineering Number	444030B41M030
Reference - Drawing Numbers	
Sales Drawing	1200878716-000, 1200878854-00P

EU ELV
Not Reviewed

EU RoHS | **China RoHS**
Not Reviewed

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
120087 Series

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION