

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0313721100

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Hybrid Receptacle Assembly, 10 Circuit, Gray, Polarization B, without CPA

Documents:

3D Model

Application Specification AS-31372-100-001 (PDF)

Drawing (PDF)

Application Specification AS-34729-020-001 (PDF)

3D Model (PDF)

Packaging Specification PK-31300-931-001 (PDF)

Product Specification PS-31372-100-001 (PDF)

Brochure (PDF)

Application Specification 347290200-AS-CH-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	31372
Application	Automotive, Power, Wire-to-Board
Comments	Polarization B, 6 x 1.50 and 4 x 2.8
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64
UPC	883906883416
Physical	
Circuits (maximum)	10
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	8.060/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm, 5.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C
Electrical	
Current - Maximum per Contact	22.0A, 30.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	347290200-AS-CH-000, AS-31372-100-001, AS-34729-020-001
Packaging Specification	PK-31300-931-001
Product Specification	PS-31372-100-001
Sales Drawing	313729000-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

31372 Series

Mates With

Stac64 Right Angle Assembly [34696](#) .

Stac64 Vertical Assembly [34695](#)

Use With

MX150 Terminal [33012](#)