

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0346950100

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Single Bay Vertical Power Header, 10 Circuits, Polarization A, Black, Tray

Documents:	
3D Model	Application Specification 347290200-AS-CH-000 (PDF)
3D Model (PDF)	Application Specification AS-34729-020-001 (PDF)
Drawing (PDF)	Brochure (PDF)
Product Specification PS-31372-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	34695
Application	Automotive, Power, Wire-to-Board
Comments	Polarization A
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64
UPC	800756894430

Physical	
Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	8.552/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.36mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	3.50mm, 5.25mm
Pitch - Termination Interface	3.50mm, 5.25mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +100°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	18.0A, 30.0A
Voltage - Maximum	500V



Series image - Reference only

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
34695 Series

Mates With
31372 5.25mm (.206") Pitch Hybrid Receptacle Assembly

Solder Process Data

Duration at Max. Process Temperature (seconds)	040
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	347290200-AS-CH-000, AS-34729-020-001
Product Specification	PS-31372-100-001
Sales Drawing	SD-34695-100-001, SD-34707-200-001, SD-34707-300-001, SD-34707-400-001

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION