

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0349600200

Status:


Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Unsealed 2 Bay Right-Angle Headers, 68 Circuits, Bay A 34 Circuit Hybrid Header, Polarization Option A, Black; Bay B 34 Circuit Hybrid Header, Polarization Option B, Gray; Tray



- Documents:
- 3D Model

Application Specification AS-34959-001-001 (PDF)
- Drawing (PDF)

Packaging Specification PK-31302-070-001 (PDF)
- 3D Model (PDF)

Datasheet (PDF)
- Product Specification PS-34959-001-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification 349590001-AS-CH-000 (PDF)

General	
Product Family	PCB Headers
Series	34960
Application	Automotive, Power, Signal, Wire-to-Board
Comments	0.50mm blades = 4.0A; 1.20mm blades = 16.0A
Overview	Mini50 Connection Systems
Product Name	Mini50
UPC	887191714967
Physical	
Breakaway	No
Circuits (Loaded)	68
Circuits (maximum)	68
Color - Resin	Black, Gray
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	13.790/g
Number of Rows	3
Orientation	Right Angle
PC Tail Length	2.75mm
PCB Locator	Yes
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	16.0A, 4.0A
Voltage - Maximum	500V DC

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34960 Series

Mates With

34959 Mini50 Unsealed 3 Row Receptacle

Material Info

Reference - Drawing Numbers

Application Specification	349590001-AS-CH-000, AS-34959-001-001
Packaging Specification	PK-31302-070-001
Product Specification	PS-34959-001-001
Sales Drawing	SD-34960-0200-001

This document was generated on 08/03/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION