

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0194180011](#)
Status: **Active**
Overview: [MX150L Industrial Sealed Connector System](#)
Description: MX150L 6 Circuit Receptacle for 18-22 AWG Wire, with CPA, Black

Documents:

3D Model	Application Specification AS-19417-001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-19418-001-001 (PDF)
Drawing (PDF)	Brochure (PDF)
Product Specification PS-19417-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E152602

General

Product Family	Crimp Housings
Series	19418
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L Industrial Sealed Connector System
Product Name	MX150L
UPC	822348005918

Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	16.672/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact	18.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	AS-19417-001-001
Packaging Specification	PK-19418-001-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19418-004-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19418](#) Series

Mates With

[19419](#) Plug, [19429](#) Panel Mount Plug

Use With

[19420](#) Female Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION