

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039000067](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Family Power Connectors](#)  
**Description:** [Mini-Fit Male Crimp Terminal, Tin \(Sn\) over Phosphor Bronze, 22-28 AWG, Reel](#)

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 55560001-AS-000 (PDF)</a>
<a href="#">Product Specification 55560002-PS-CH-000 (PDF)</a>	<a href="#">Packaging Specification 55580001-PK-000 (PDF)</a>
<a href="#">Product Specification 55560002-PS-ES-000 (PDF)</a>	<a href="#">Test Summary 55560010-TS-000 (PDF)</a>
<a href="#">Product Specification 55560002-PS-SK-000 (PDF)</a>	<a href="#">Test Summary TS-5556-002-001 (PDF)</a>
<a href="#">Product Specification PS-5556-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-5556-002-001 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	<a href="#">5558</a>
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Family Power Connectors</a>
Packaging Alternative	<a href="#">39000068 (Loose)</a>
Product Name	Mini-Fit
UPC	800754394024

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.120/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Solder Process Data**


Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	5558-PBT2
--------------------	-----------

**Reference - Drawing Numbers**

Application Specification	<a href="#">55560001-AS-000</a>
Packaging Specification	<a href="#">55580001-PK-000</a>
Product Specification	<a href="#">55560002-PS-CH-000</a> , <a href="#">55560002-PS-ES-000</a> , <a href="#">55560002-PS-SK-000</a> , <a href="#">PS-5556-001-001</a> , <a href="#">PS-5556-002-001</a>
Sales Drawing	<a href="#">SD-5558XXXX-001</a>
Test Summary	<a href="#">55560010-TS-000</a> , <a href="#">TS-5556-002-001</a>



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5558 Series](#)

**Use With**

Mini-Fit Jr. Plug Housing [5559](#) <br>Mini-Fit  
BMI Plug Housing [42475](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool for	<a href="#">11030044</a>
Mini-Fit Jr. Terminals	
PremiumGrade Hand	<a href="#">638191000</a>
Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 22-28 AWG	
FineAdjust Applicator	<a href="#">639002700</a>
for Insulation OD	

1.30-1.50mm, 22-28 AWG Wire FineAdjust Applicator	<u>639020200</u>
for Insulation OD 1.10-1.30mm - 22-28 AWG FineAdjust Applicator	<u>639023800</u>
for Insulation OD 0.95-1.08mm - 22-28 AWG T2 Terminator	<u>639102700</u>
for Insulation OD 1.30-1.50mm, 22-28 AWG T2 Terminator	<u>639120200</u>
for insulation OD 1.10-1.30mm - 22-28 AWG T2 Terminator	<u>639123800</u>
for insulation OD 0.95-1.08mm - 22-28 AWG	
<b>Japan</b>	
<b>Description</b>	<b>Product #</b>
Applicator for M21 1A Bench Press, 22-28	<u>570383000</u>
AWG Wire	

This document was generated on 08/17/2021

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**