

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0039000079**  
**Status:** **Active**  
**Overview:** Mini-Fit Family Power Connectors  
**Description:** Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 16, 18+22, 20+20, 20+22 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-5556-002-001 (PDF)</a>
<a href="#">Product Specification 55560002-PS-CH-000 (PDF)</a>	<a href="#">Application Specification 55560001-AS-000 (PDF)</a>
<a href="#">Product Specification 55560002-PS-ES-000 (PDF)</a>	<a href="#">Packaging Specification 55560001-PK-000 (PDF)</a>
<a href="#">Product Specification 55560002-PS-SK-000 (PDF)</a>	<a href="#">Test Summary 55560010-TS-000 (PDF)</a>
<a href="#">Product Specification 55560008-TS-000 (PDF)</a>	<a href="#">Test Summary TS-5556-002-001 (PDF)</a>
<a href="#">Product Specification PS-5556-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	5556
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Family Power Connectors</a>
Packaging Alternative	<a href="#">39000080 (Loose)</a>
Product Name	Mini-Fit
UPC	800753749986

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.162/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16, 18+22, 20+20, 20+22
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number	5556PBT3
--------------------	----------

**Reference - Drawing Numbers**

Application Specification	55560001-AS-000
Packaging Specification	55560001-PK-000
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, 55560008-TS-000, PS-5556-001-001, PS-5556-002-001
Sales Drawing	55560000-SD-000
Test Summary	55560010-TS-000, TS-5556-002-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5556 Series](#)

**Use With**

Mini-Fit Jr. Receptacle Housing [5557](#)  
<br>Mini-Fit BMI Slide and Lock Panel  
Mount [44516](#) <br>Mini-Fit BMI Panel Mount  
Receptacle Housing<br> [42474](#) , [43760](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool for Mini-Fit Jr. Terminals	<a href="#">11030044</a>
Hand Crimp Tool for Mini-Fit Jr. Male and Female Crimp Terminals, 16 AWG	<a href="#">2002182200</a>
FineAdjust Applicator for Mini-Fit Double	<a href="#">2037026200</a>

Crimp Applications  
Using Two 20 & 22  
AWG, 20 & 20 AWG,  
or 18 & 22 AWG  
Wires

FineAdjust Applicator [639039400](#)  
for Insulation OD  
2.20-2.45mm,  
Optimized for 16  
AWG Only

FineAdjust Applicator [639041400](#)  
for Mini-Fit Jr., Mini-  
Fit HCS, and Mini-  
Fit Plus HCS Crimp  
Terminals, 16 AWG  
with Large Insulation  
Diameters

FineAdjust [639041500](#)  
Applicator for Mini-  
Fit Crimp Terminals,  
1.80-2.20mm  
Insulation Diameter  
Wire, 16 AWG,  
1.31mm<sup>2</sup>

**Japan**

<b>Description</b>	<b>Product #</b>
--------------------	------------------

Applicator for M21 1A Bench Press, 18-24 AWG Wire	<a href="#">570223000</a>
---	---------------------------

This document was generated on 08/16/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**