

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022032161

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 254 Wire-to-Board Header, Single Row, Vertical, 16 Circuits, PA Polyamide Nylon, Tin (Sn) Plating

Documents:

- 3D Model

Product Specification PS-10-07-001 (PDF)
- 3D Model (PDF)

Packaging Specification PK-4030-001-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

4030

Application

Board-to-Board, Signal, Wire-to-Board

Overview

KK Interconnect Solutions

Product Name

KK 254

UPC

800753735347

Physical

Breakaway

No

Circuits (Loaded)

16

Circuits (maximum)

16

Color - Resin

Natural (White)

Durability (mating cycles max)

25

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

1.098/g

Number of Rows

1

Orientation

Vertical

PC Tail Length

3.43mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Plating min - Mating

5.080µm

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Stackable

Yes

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

4.0A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

4030 Series

Mates With

2695 , 6471 , 7880 , 4455 , 7720

Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	A-4030-16A197
Reference - Drawing Numbers	
Packaging Specification	PK-4030-001-001
Product Specification	PS-10-07-001
Sales Drawing	SD-4030-0001-001

This document was generated on 02/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION