

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026481046

Status:

Active

Overview:


KK Interconnect Solutions

Description:

KK 396 Breakaway Header, Right-Angle with Friction Lock, 4 Circuits, Tin (Sn) Plating

Documents:	
3D Model	Product Specification PS-08-50-001 (PDF)
Drawing (PDF)	Packaging Specification PK-41672-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
Application tooling part link	
Application Tooling Part Link	11-20-0901
General	
Product Family	PCB Headers
Series	41672
Application	Power, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 396
UPC	800753586499
Physical	
Breakaway	Yes
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Resin	Polyester
Net Weight	1.684/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	5.38mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Polarized to Mating Part	No
Polarized to PCB	Yes
Shrouded	No
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	7.0A
Voltage - Maximum	250V



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

41672 Series

Mates With

2139 KK Crimp Housing, 41695 KK Crimp Housing, 6442 KK Crimp Housing, 2145 PCB Connector, 41815 PCB Connector, 3069 KK Crimp Housing

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	A-41672-A04A197
--------------------	-----------------

Reference - Drawing Numbers

Packaging Specification	PK-41672-001-001
Product Specification	PS-08-50-001
Sales Drawing	SD-41672-001-001

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION