

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0460123141](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: [Mini-Fit Plus Crimp Terminal, 16 AWG, Reel, Tin \(Sn\) Plating](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-46012-001-001 \(PDF\)](#)
[Product Specification PS-45750-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	46012
Application	Power, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current de-rating information.
Crimp Quality Equipment Overview	Yes
Packaging Alternative	Mini-Fit Family Power Connectors
Product Name	460123142 (Bag)
UPC	Mini-Fit Plus 822350570459

Physical

Durability (mating cycles max)	100
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.145/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.15mm
Wire Size AWG	16
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-46012-001-001
Product Specification	PS-45750-001-001
Sales Drawing	SD-46012-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[46012](#) Series

Use With

Mini-Fit Jr. Plugs [5559](#)
 Mini-Fit MBI
Panel Mount Plugs [42475](#)
 Mini-Fit TPA
Plugs [30068](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Mini-Fit Jr. Terminals	11030044
Hand Crimp Tool for Mini-Fit Jr. Male and Female Crimp Terminals, 16 AWG	2002182200
FineAdjust Applicator for Insulation OD 2.20-2.45mm,	639039400

Optimized for 16
AWG Only
FineAdjust Applicator 639041400
for Mini-Fit Jr., Mini-
Fit HCS, and Mini-
Fit Plus HCS Crimp
Terminals, 16 AWG
with Large Insulation
Diameters
FineAdjust 639041500
Applicator for Mini-
Fit Crimp Terminals,
1.80-2.20mm
Insulation Diameter
Wire, 16 AWG,
1.31mm²

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION