

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0473461001

Status:

Active

Overview:

USB Products and Solutions

Description:

Micro-USB B Receptacle without Flange, Bottom Mount, Surface Mount, Lead-Free

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-47346-001-001 (PDF)

Packaging Specification PK-47346-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E107635

General

Product Family

Series

Application

Comments

Component Type

Overview

Product Name

Standard

Type

UPC

I/O Connectors

47346

Wire-to-Board

Signal contacts 1.0A, Power contacts 1.8A

Receptacle

USB Products and Solutions

USB

USB 2.0

Micro-B

887191074382

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Gender

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Mounting Style

Net Weight

Number of Rows

Orientation

PCB Retention

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Ports

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Waterproof / Dustproof

5

5

Black

10000

94V-0

Female

Yes

No

Copper Alloy

Gold

Gold

High Temperature Thermoplastic

Bottom-Mount

0.247/g

1

Right Angle

None

Embossed Tape on Reel

No

0.65mm

0.65mm

Yes

1

Yes

-30° to +85°C

Surface Mount

No


Electrical

Current - Maximum per Contact

Grounding to Panel

1.8A, 1.0A

Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

47346 Series

Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)

Solder Process Data

Duration at Max. Process Temperature (seconds)	003
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	255

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-47346-001-001
Product Specification	PS-47346-001-001
Sales Drawing	SD-47346-001-001

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION