

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0541043531

Status: Active

Overview: Easy-On FFC FPC Connectors

Description: Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Top Contact, 2.00mm Height, 35 Circuits, Gold Plating



- Documents:**
- | | |
|---|--|
| Drawing (PDF) | Datasheet (PDF) |
| 3D Model | Product Guide (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-54104-071-001 (PDF) | Reference Guide (PDF) |
| Packaging Specification SPK-54104-001-001 (PDF) | |

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	FFC/FPC Connectors
Series	54104
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	Slider
UPC	822348689040

Physical

Actuator Type	Slider
Circuits (Loaded)	35
Color - Resin	Natural
Contact Position	Top
Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	2.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	405.195/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-20° to +85°C
Wire/Cable Type	FFC/FPC

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Material Info

Reference - Drawing Numbers

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

54104 Series

Mates With

Premo-Flex FFC Cable 15020

Packaging Specification
Product Specification
Sales Drawing

SPK-54104-001-001
PS-54104-071-001
541040000-000, 541041000-000

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION