

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **5601240101**  
**Status:** **Active**  
**Overview:** DuraClik Connector System  
**Description:** DuraClik ISL Wire-to-Board Crimp Receptacle Terminal, Female, AVSS 0.3 Square Wire, Tin

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Application Specification AS-560123-001-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-560124-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-560123-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-560123-003-001 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	560124
Application	Automotive, Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	<u>DuraClik Connector System</u>
Product Name	DuraClik
UPC	887191705569

**Physical**

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.063/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40mm
Wire Size AWG	22
Wire Size mm <sup>2</sup>	0.35

**Electrical**

Current - Maximum per Contact	3.0A
Voltage - Maximum	125V

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-560123-001-001
Crimp Specification	CS-560124-001-001
Packaging Specification	PK-560124-001-001
Product Specification	PS-560123-001-001, PS-560123-003-001
Sales Drawing	SD-560124-001-001



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

560124 Series

**Use With**

560123 DuraClik ISL Receptacle Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

FA2 Mechanical [638084400](#)

Feed Crimp Applicator for 2.00mm Wire-to-Board DuraClik ISL Receptacle Terminals  
 FA2 Pneumatic Feed [638084410](#)  
 Crimp Applicator for 2.00mm Wire-to-Board DuraClik

ISL Receptacle Terminals	
Extraction and Activation Tool	<u>638132700</u>
Hand Crimp Tool for DuraClik ISL Receptacle Terminal, AVSS 0.30-0.35mm <sup>2</sup> Wire	<u>638277800</u>

This document was generated on 08/24/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**