

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0525591853

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 18 Circuits, Gold Plating



Series image - Reference only

Documents:	
Drawing (PDF)	Packaging Specification 525599200-200 (PDF)
3D Model	Datasheet (PDF)
3D Model (PDF)	Product Guide (PDF)
Product Specification PS-52559-014-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 525590003-A00 (PDF)	Reference Guide (PDF)

Agency Certification	
UL	E29179
General	
Product Family	FFC/FPC Connectors
Series	52559
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	Slider
UPC	822350045315
Physical	
Actuator Type	Slider
Circuits (Loaded)	18
Color - Resin	Natural
Contact Position	N/A
Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	3.90mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	251.764/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Plating min - Mating	0.102µm
Plating min - Termination	1.016µm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Material Info

Reference - Drawing Numbers

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

52559 Series

Mates With

Premo-Flex FFC Cable 15020

Application Specification
Packaging Specification
Product Specification
Sales Drawing

525590003-A00
525599200-200
PS-52559-014-001
SD-52559-050-001

This document was generated on 08/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION