

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0526102072

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 20 Circuits, Gold Plating



Documents:	
3D Model (PDF)	Datasheet (PDF)
Drawing (PDF)	Product Guide (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
Product Specification PS-52610-007-001 (PDF)	Reference Guide (PDF)
Packaging Specification SPK-52610-003-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	FFC/FPC Connectors
Series	52610
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	Slider
UPC	822350243704
Physical	
Actuator Type	Slider
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Natural
Contact Position	N/A
Durability (mating cycles max)	30
Flammability	94V-0
Mated Height	5.75mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	929.900/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.00mm
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	125V
Material Info	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
52610 Series

Mates With
Premo-Flex FFC Cable 15039

Reference - Drawing Numbers

Packaging Specification	SPK-52610-003-001
Product Specification	PS-52610-007-001
Sales Drawing	526100000-000, 526101000-000, SD-52610-036-001

This document was generated on 08/03/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION