

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0874380243

Status:


Active

Overview:

Pico-SPOX Wire-to-Board Connector System

Description:

1.50mm Pitch, Pico-SPOX PCB Header, Single Row, Right-Angle, Surface Mount, Tin over Nickel Plating, Friction Lock, 2 Circuits, Tape and Reel, Beige



Series image - Reference only

Documents:	
3D Model (PDF)	Product Specification PS-87437-001-001 (PDF)
Drawing (PDF)	Application Specification 874370000-AS-000 (PDF)
3D Model	Packaging Specification SPK-87438-001-001 (PDF)
Product Specification 874371001-PS-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	87438
Application	Signal, Wire-to-Board
Overview	Pico-SPOX Wire-to-Board Connector System
Product Name	Pico-SPOX
UPC	822348438877
Physical	
Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Beige
Durability (mating cycles max)	10
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	135.000/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Surface Mount
Electrical	

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status Not Low-Halogen	
For more information, please visit Contact US	
China ROHS ELV	Green Image Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
87438 Series

Mates With
87439 Pico-SPOX Wire-to-Board Housing

Use With
87421 1.50mm Pico-SPOX Crimp Terminal

Current - Maximum per Contact	2.5A
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Application Specification	874370000-AS-000
Packaging Specification	SPK-87438-001-001
Product Specification	874371001-PS-001, PS-87437-001-001
Sales Drawing	874380231-SD-000

This document was generated on 08/19/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION