

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0878325922

Status:


Active

Overview:

Milli-Grid Connector System

Description:

2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Vertical, Surface Mount, Shrouded, Lead-Free, 20 Circuits, 0.38µm Gold (Au) Plating, with Pick-and-Place Cap, with Side and Center Locking Windows, with Center Polarization Slot, with PCB Locator, Embossed



|                                                                  |                                                                |
|------------------------------------------------------------------|----------------------------------------------------------------|
| Documents:                                                       |                                                                |
| <a href="#">3D Model</a>                                         | <a href="#">Packaging Specification PK-87831-001-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                    | <a href="#">Packaging Specification PK-87832-300-001 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                                   | <a href="#">Datasheet (PDF)</a>                                |
| <a href="#">Product Specification PS-87831-027-001 (PDF)</a>     | <a href="#">RoHS Certificate of Compliance (PDF)</a>           |
| <a href="#">Application Specification 503940001-AS-000 (PDF)</a> |                                                                |

|                                |                                                               |
|--------------------------------|---------------------------------------------------------------|
| Agency Certification           |                                                               |
| CSA                            | LR19980                                                       |
| UL                             | E29179                                                        |
| General                        |                                                               |
| Product Family                 | PCB Headers                                                   |
| Series                         | 87832                                                         |
| Application                    | Signal, Wire-to-Board                                         |
| Comments                       | With Cap Contact Molex for application in automotive industry |
| Overview                       | <a href="#">Milli-Grid Connector System</a>                   |
| Product Name                   | Milli-Grid                                                    |
| UPC                            | 822348232031                                                  |
| Physical                       |                                                               |
| Breakaway                      | No                                                            |
| Circuits (Loaded)              | 20                                                            |
| Circuits (maximum)             | 20                                                            |
| Color - Resin                  | Black                                                         |
| Durability (mating cycles max) | 100                                                           |
| First Mate / Last Break        | No                                                            |
| Flammability                   | 94V-0                                                         |
| Glow-Wire Capable              | No                                                            |
| Guide to Mating Part           | No                                                            |
| Keying to Mating Part          | Yes                                                           |
| Lock to Mating Part            | Yes                                                           |
| Material - Metal               | Phosphor Bronze                                               |
| Material - Plating Mating      | Gold                                                          |
| Material - Plating Termination | Tin                                                           |
| Material - Resin               | Nylon                                                         |
| Net Weight                     | 0.900/g                                                       |
| Number of Rows                 | 2                                                             |
| Orientation                    | Vertical                                                      |
| PCB Locator                    | No                                                            |
| PCB Retention                  | None                                                          |
| Packaging Type                 | Embossed Tape on Reel                                         |
| Pitch - Mating Interface       | 2.00mm                                                        |
| Pitch - Termination Interface  | 2.00mm                                                        |
| Plating min - Mating           | 0.381µm                                                       |
| Plating min - Termination      | 1.905µm                                                       |
| Polarized to PCB               | No                                                            |
| Robotic Placement              | Pick and Place Cap                                            |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2020)9139-DC (19 Jan 2021)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

87832 Series

Mates With

Milli-Grid Vertical Through Hole Receptacle [79107](#) , [78787](#) , Milli-Grid Flex-to-Board Vertical Receptacle [79108](#) , Milli-Grid Vertical Surface Mount Receptacle [79109](#) , [78788](#) , Milli-Grid Crimp Housing [51110](#) , Milli-Grid Cable-to-Board Receptacle [87568](#)

|                                                |                                    |
|------------------------------------------------|------------------------------------|
| Shrouded                                       | Fully                              |
| Stackable                                      | No                                 |
| Surface Mount Compatible (SMC)                 | Yes                                |
| Temperature Range - Operating                  | -55° to +105°C                     |
| Termination Interface: Style                   | Surface Mount                      |
| <b>Electrical</b>                              |                                    |
| Current - Maximum per Contact                  | 2.0A                               |
| Voltage - Maximum                              | 125V                               |
| <b>Solder Process Data</b>                     |                                    |
| Duration at Max. Process Temperature (seconds) | 010                                |
| Lead-freeProcess Capability                    | REFLOW                             |
| Max. Cycles at Max. Process Temperature        | 001                                |
| Process Temperature max. C                     | 260                                |
| <b>Material Info</b>                           |                                    |
| <b>Reference - Drawing Numbers</b>             |                                    |
| Application Specification                      | 503940001-AS-000                   |
| Packaging Specification                        | PK-87831-001-001, PK-87832-300-001 |
| Product Specification                          | PS-87831-027-001                   |
| Sales Drawing                                  | SD-87832-0001-001                  |

This document was generated on 08/19/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**