

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0855135001

Status:


Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Jack, Vertical, Top Entry, Surface Mount, 8/8, Low Profile, 15" Reel



Series image - Reference only

Documents:	
3D Model	Application Specification AS-85513-001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-85513-001-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification PS-85513-002-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification		
UL		E107635
General		
Product Family		Modular Jacks/Plugs
Series		85513
Comments		Reflow Capable, Small Panel Cutout
Component Type		PCB Jack
Magnetic		No
Overview		Magnetic and Modular Jacks/Plugs
Performance Category		3
Power over Ethernet (PoE)		N/A
Product Name		Modular Jack 8/8, RJ45
UPC		822350803496
Physical		
Boot Color		N/A
Color - Resin		Black
Durability (mating cycles max)		2500
Flammability		94V-0
Inverted / Top Latch		No
Jack Height		12.70mm
Lightpipes/LEDs		None
Material - Metal		Copper Alloy
Material - Plating Mating		Gold over Palladium Nickel
Material - Plating Termination		Tin
Material - Resin		High Temperature Thermoplastic
Net Weight		2.879/g
Orientation		Vertical (Top Entry)
PCB Locator		No
PCB Retention		Yes
Packaging Type		Embossed Tape on Reel
Pitch - Mating Interface		1.02mm
Pitch - Termination Interface		1.27mm
Plating min - Mating		0.051µm, 1.016µm
Plating min - Termination		1.905µm
Port Configuration		1x1
Positions / Loaded Contacts		8/8
Surface Mount Compatible (SMC)		Yes
Temperature Range - Operating		-40° to +85°C
Termination Interface: Style		Surface Mount
Waterproof / Dustproof		No
Wire/Cable Type		N/A
Electrical		
Current - Maximum per Contact		1.5A

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

85513 Series

Mates With

90075 Modular Plug

Shielded	No
Voltage - Maximum	125V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	045
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-85513-001-001
Packaging Specification	PK-85513-001-001
Product Specification	PS-85513-002-001
Sales Drawing	SD-85513-010-001

This document was generated on 08/19/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION