

## SUBJECT: SCOPE OF DOCUMENT

### CONTAINS :

1-0. General Description

2-0. Input Requirements

3-0. Output Requirements

4-0. Reliability

5-0. Environment

6-0. Safety

7-0. Mechanical Characteristics

## 1-0. General Description

The purpose of the document is to specify a Single phase AC input, single output switching power supply. This specification is suitable for: EA11811K series  
This product is AC to DC switching power transfer device, it can provide for a 24V, 8.33A max & 200W max DC output with constant voltage source.  
This Specification defines the input, output, performance characteristics, environment, noise and safety requirement for a power supply.

## 2-0. Input Requirements

### 2-1. Input Voltage

Rated Voltage 100-240 Vac +/- 10% full range.

Normal line input 115Vac/60Hz, 230Vac/50Hz.

### 2-2. Input Frequency

47~63 Hz

### 2-3. Input Current

a. 2.5A(Max.) @ 115Vac input with full load.

b. 1.3A(Max.) @ 230Vac input with full load.

### 2-4. Energy saving standards:

#### 2-4-0. Designed to meet the following standard :

CoC Tier 2

#### 2-4-1. Efficiency

Efficiency 89% (AVG.) normal input & 25%, 50%, 75% ,100% of max output load

#### 2-4-2 No Load Power Consumption.

No Load Watt 0.15W at normal line input.

### 2-5. Configuration

3-wire AC input (Line , Neutral, FG)

### 2-6. Input Fuse

The hot line side of the input shall have a fuse, rating (6.3A/250V)

### 2-7. Inrush Current

60A at 110 Vac At cold start, maximum load.

120A at 220 Vac At cold start, maximum load.

### 2-8. Line Regulation

This line regulation is less than  $\pm 1\%$ , of rated output voltage @ full load .

## 2-9. Hold Up Time

8.3mSec. @ Normal line, with full load.

## 2-10. Rise Time

50 mSec., @ 100-240VAC input, with full load from 10% to 90% of output voltage.

## 2-11. Turn-ON Time

The output voltage should rise to 90% of rated output voltage in less than 3 SEC. from AC apply to 110Vac start up.

## 2-12. Harmonic Standard and Power Factor

The adapter complied with IEC 61000-3-2 class D harmonic standard while input power over than 75W. The P.F. shall  $>0.95$  @100Vac input and  $>0.9$  @240Vac input.

## 3-0. Output Requirements

### 3-1. Output Voltage and Current

Output Voltage (Vdc)	Current Min.(A)	Current Max.(A)
+24V	0	8.33

### 3-2. Load Regulation

Voltage (Vdc)	Tolerance (%)
+24V	+5/, -5

### 3-3. Dynamic Load Regulation

$\pm 5\%$  excursion for 50% - 100% or 100% - 50% load change of DC output at any frequency up to 1KHz(duty 50%).

### 3-4. Ripple & Noise

The power supply shall not exceed the following limits on the indicated voltage for 60Hz or 50Hz ripple, Switching frequency ripple and noise and dynamic load variations measured with a 20MHz bandwidth

Output	Ripple/Noise
+23V	1% max. of rated output voltage

Input condition : for rated voltage , Output condition : for max load

Ripple / Noise: 60Hz ripple + switching ripple and noise

Ripple & Noise are measured at the end of output cable which are added a 0.1uF ceramic capacitor and a 47uF electrolytic capacitor

### 3-5. Over Voltage Protection

150% Max. of rated voltage.

The output voltage shall shutdown and latch-off when OVP is occurred.

### 3-6. Over Current Protection

110% --- 170% of rated output current.

The output voltage shall shutdown and latch-off when OCP is occurred.

### 3-7. Stability

2% Max. at constant load with constant input (after 30 minutes of operation).

### 3-8. Temperature Rise

Less than 45 °C on top/bottom case at normal AC input & 80% load of DC output at environment temperature 25 °C.

### 3-9. Drop-out (Power Line Disturbance)

Output voltage shall remain within the specified regulation range, through the absence of a line input during 1/2 cycle, at full load and normal AC line input

### 3-10. Voltage Isolation

The DC ground will be isolated from the AC neutral and AC line.

## 4-0. Reliability

### 4-1. MTBF ( MIL-HDBK-217F )

The power supply shall be designed and produced to have a mean time between failure ( MTBF) of 100,000 hours at 25 degrees C.

## 5-0. Environment

### 5-1 Temperature

a. Operating : 0 °C to 40 °C

b. Storage : -20 to 85 °C

### 5-2 Humidity

a. Operating : 10 to 90 %

b. Storage: 5 to 90 %

### 5-3 Altitude

From sea level to 5,000 Meter (operation ) and 5,000 Meter (non operation )

6-0. Safety

6-1. Hi-Pot Test

3000Vac, 10mA, 2Sec between primary and secondary circuit

6-2. Insulation Test

500Vdc, 2Sec. between primary and secondary circuit

IR should 50 M .

6-3. Leakage Current

250uA at 240Vac/50 Hz

6-4. Safety

UL, CUL, TUV, CB, CE, FCC

6-5. EMS

Items	Specification	Reference
ESD	Contact: $\pm 4\text{KV}$	IEC 61000-4-2
	Air: $\pm 8\text{KV}$	
RS	Frequency: 80~1000MHz Field Strength: 3V/M, 80% AM(1KHz)	IEC 61000-4-3
EFT	1.0 KV on input AC power ports.	IEC 61000-4-4
SURGE	Line to Line: $\pm 1\text{KV}$ (peak)	IEC 61000-4-5
	Line to F.G : $\pm 2\text{KV}$ (peak)	

6-6. EMI

Comply with Standards
CISPR 32, EN 55032 Class B FCC PART 15 Class B

7-0. Mechanical Characteristics

7-1. Physical Size : 166 \* 83\* 28 mm

7-2. Enclosure material : 94V-0 minimum

7-3. Output Cable (Reference) : UL1185 #16





#### 7-4. Vibration Test

The vibration frequencies are set at 20Hz, with total amplitude of 1.5mm  
Along the 3 directions namely X-Y-Z. The each direction should be vibrated  
for 60 minutes, after testing no abnormal electrical or mechanical should occur.

#### 7-5. Drop Test (Referencing to CSA C22.2 No.950/UL1950/UL1310/EN62368)

Products shall be dropped from a height of 1000 mm onto a horizontal surface  
consists of hardwood at 13mm thick , mounted on two layers of plywood each  
19mm to 20mm thick , all supported on a concrete or equivalent non-resilient  
floor. Upon conclusion of test , the equipment cannot into hazardous moving  
parts and hazardous voltage circuits need be operational , and need meet Hi-Pot  
specification requirement .

#### 7-6. Net Weight (Reference) : 750g



EDAC POWER ELEC.				APPROVED
MODEL	EA11811K(T02)	UNIT	mm	DESIGNED
color	BLACK	SCALE		CHECK
cus.		DATE	2020-05-25	DRAWING L.J.YU

100+/-1


**EDAC** EDACPOWER ELEC.

AC ADAPTER

MODEL : EA11811K-240

AC INPUT : 100-240V~, 2.5A, 50-60Hz

DC OUTPUT : 24.0V ==8.33A 200.0W



**CAUTION**

FOR INDOOR USE ONLY

I.T.E. USE ONLY

DATE CODE:

20	21	22			1	2	3	4	5
1	2	3	4	5	6	7	8	9	0

1312

C1 C3 MADE IN CHINA




I.T.E. POWER SUPPLY  
41TJ  
E209833



**RoHS**

50+/-1

R22\*3



EDAC P/N.: 312

Background: Black color

Character: Silver color

Unit: mm