

Heat Shrink Tube Assortments 2:1 (1600 pcs) Type: 2109CA136

This range of shrinking tubes is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs. 2 x 800 pieces of shrinking ratio 2:1 standard shrinking tube for a range of application diameter from 1.5 to 12 mm.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used. High quality product from industrial applications.



Technical Specifications

Material: PE, shrink temperature (min.): 70 °C, shrink temperature (max.): 110 °C, operating temperature: -40 °C to +125 °C, tensile strength (min.): 10.4 MPa, dielectric strength 1.5 kV (30 sec.), industrial quality. All hoses comply with RoHS directives and are halogen-free. Further technical data on the components included, are printed on the inside of the covers.

Content

Two transparent assortment boxes, min. 800 heat shrink tubing sections per each assortment.

600 pieces - Ø 1.5 mm - length 45 mm, 440 pieces - Ø 2.5 mm - length 45 mm, 120 pieces - Ø 3.5 mm - length 65 mm, - 60 pieces - Ø 5 mm - length 65 mm, 50 pieces - Ø 6 mm - length 45 mm, 110 pieces - Ø 8 mm - length 45 mm, 110 pieces - Ø 9 mm length - 65 mm, 110 pieces - Ø 12 mm length - 65 mm.