

Safety Data Sheet

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Mixture identification:

Trade name: Ink, C13T00P240

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use:

Ink for inkjet printing

1.3. Details of the supplier of the safety data sheet

Company:

EPSON EUROPE B.V.

Azie building, Atlas ArenA, Hoogoorddreef 5, 1101 BA Amsterdam

Zuidoost The Netherlands

Phone number: +31-20-314-5000

Competent person responsible for the safety data sheet:

chemicals@epson-europe.com

Date: 06/07/2018

Revision: 1.0

1.4. Emergency telephone number

Phone number: +31-20-314-5000

United Kingdom; 01952 607111 Monday to Friday 9am to 5:30pm.

Emergency Action: In the event of a medical enquiry involving this product, please contact your doctor or local hospital accident and emergency department.

Ireland; +353 (01) 809 2566 or +353 (01) 809 2166

Malta; 2545 0000 or 21224071

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

EC regulation criteria 1272/2008 (CLP)

The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).

Adverse physicochemical, human health and environmental effects:

No other hazards

2.2. Label elements

The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).

Hazard pictograms:

None

Hazard statements:

None

Precautionary statements:

None

Special Provisions:

EUH210 Safety data sheet available on request.

EUH208 Contains 2,4,7,9-tetramethyldec-5-yne-4,7-diol. May produce an allergic reaction.

Special provisions according to Annex XVII of REACH and subsequent amendments:

None

2.3. Other hazards

vPvB Substances: None - PBT Substances: None

Other Hazards:

No other hazards

SECTION 3: Composition/information on ingredients




Safety Data Sheet

3.1. Substances

No

3.2. Mixtures

Hazardous components within the meaning of the CLP regulation and related classification:

Qty	Name	Ident. Number	Classification
50% ~ 65%	Water	CAS: 7732-18-5 EC: 231-791-2	The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).
10% ~ 12.5%	Glycerol	CAS: 56-81-5 EC: 200-289-5	The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).
7% ~ 10%	2-[2-(2-butoxyethoxy)ethoxy]ethanol; TEGBE; triethylene glycol monobutyl ether	Index number: 603-183-00-0 CAS: 143-22-6 EC: 205-592-6 REACH No.: 01-21194751 07-38	 3.3/1 Eye Dam. 1 H318
1% ~ 3%	E-C104	EC: 700-815-8 REACH No.: 01-21199296 31-38	4.1/C3 Aquatic Chronic 3 H412
0.1% ~ 0.25%	2,4,7,9-tetramethyldec-5-yne-4,7-diol	CAS: 126-86-3 EC: 204-809-1	 3.3/1 Eye Dam. 1 H318  3.4.2/1B Skin Sens. 1B H317 4.1/C3 Aquatic Chronic 3 H412
0.1% ~ 0.25%	Triethanol amine	CAS: 102-71-6 EC: 203-049-8	The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).

SECTION 4: First aid measures

4.1. Description of first aid measures

In case of skin contact:

Wash with plenty of water and soap.

In case of eyes contact:

In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

In case of Ingestion:

Do not under any circumstances induce vomiting. OBTAIN A MEDICAL EXAMINATION IMMEDIATELY.

In case of Inhalation:

Remove casualty to fresh air and keep warm and at rest.

4.2. Most important symptoms and effects, both acute and delayed

None

4.3. Indication of any immediate medical attention and special treatment needed

Treatment:

None

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Water.

Carbon dioxide (CO₂).

Extinguishing media which must not be used for safety reasons:

None in particular.

Safety Data Sheet

- 5.2. Special hazards arising from the substance or mixture
 - Do not inhale explosion and combustion gases.
 - Burning produces heavy smoke.
- 5.3. Advice for firefighters
 - Use suitable breathing apparatus .
 - Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
 - Move undamaged containers from immediate hazard area if it can be done safely.

SECTION 6: Accidental release measures

- 6.1. Personal precautions, protective equipment and emergency procedures
 - Wear personal protection equipment.
 - Remove persons to safety.
 - See protective measures under point 7 and 8.
- 6.2. Environmental precautions
 - Do not allow to enter into soil/subsoil. Do not allow to enter into surface water or drains.
 - Retain contaminated washing water and dispose it.
 - In case of gas escape or of entry into waterways, soil or drains, inform the responsible authorities.
 - Suitable material for taking up: absorbing material, organic, sand
- 6.3. Methods and material for containment and cleaning up
 - Wash with plenty of water.
- 6.4. Reference to other sections
 - See also section 8 and 13

SECTION 7: Handling and storage

- 7.1. Precautions for safe handling
 - Avoid contact with skin and eyes, inhalation of vapours and mists.
 - Don't use empty container before they have been cleaned.
 - Before making transfer operations, assure that there aren't any incompatible material residuals in the containers.
 - Contaminated clothing should be changed before entering eating areas.
 - Do not eat or drink while working.
 - See also section 8 for recommended protective equipment.
- 7.2. Conditions for safe storage, including any incompatibilities
 - Keep away from food, drink and feed.
 - Incompatible materials:
 - None in particular.
 - Instructions as regards storage premises:
 - Adequately ventilated premises.
- 7.3. Specific end use(s)
 - None in particular

SECTION 8: Exposure controls/personal protection

- 8.1. Control parameters
 - Glycerol - CAS: 56-81-5
 - OEL Type: OSHA - TWA: 5 mg/m³ - Notes: Respirable dust
 - OEL Type: OSHA - TWA: 15 mg/m³ - Notes: Total dust
 - Triethanol amine - CAS: 102-71-6
 - OEL Type: ACGIH - TWA(8h): 5 mg/m³
 - DNEL Exposure Limit Values
 - No data available
 - PNEC Exposure Limit Values

Safety Data Sheet

10.3. Possibility of hazardous reactions	None
10.4. Conditions to avoid	Stable under normal conditions.
10.5. Incompatible materials	None in particular.
10.6. Hazardous decomposition products	None.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological information of the product:

- e) germ cell mutagenicity: Test: Mutagenesis - Species: Salmonella Typhimurium and Escherichia coli Negative
- f) carcinogenicity: Does not contain carcinogens (Ref. 1)
- g) reproductive toxicity: Does not contain reproductive toxicity and developmental toxic substances (Ref. 2)

Toxicological information of the main substances found in the product:

Glycerol - CAS: 56-81-5

a) acute toxicity:

Test: LD50 - Route: Oral - Species: Guinea pig = 7750 mg/kg - Source: Journal of Industrial Hygiene and Toxicology. Vol. 23, Pg. 259, 1941

Test: LDLo - Route: Oral - Species: Human = 1428 mg/kg - Source: "Toxicology of Drugs and Chemicals," Deichmann, W.B., New York, Academic Press, Inc., 1969Vol. -, Pg. 288, 1969.

2-[2-(2-butoxyethoxy)ethoxy]ethanol; TEGBE; triethylene glycol monobutyl ether - CAS: 143-22-6

a) acute toxicity:

Test: LD50 - Route: Dermal - Species: Rabbit = 3.54 ml/kg - Source: American Industrial Hygiene Association Journal. Vol. 23, Pg. 95, 1962.

Test: LD50 - Route: Oral - Species: Rat = 5300 mg/kg - Source: Office of Toxic Substances Report. Vol. OTS,

2,4,7,9-tetramethyldec-5-yne-4,7-diol - CAS: 126-86-3

a) acute toxicity:

Test: LD50 - Route: Dermal - Species: Rat > 2000 mg/kg

b) skin corrosion/irritation:

Test: Skin Irritant - Species: Rabbit Mild irritant

c) serious eye damage/irritation:

Test: Eye Irritant - Species: Rabbit Highly irritating

d) respiratory or skin sensitisation:

Test: Skin Sensitisation - Route: LLNA - Species: Mouse Sensitiser

e) germ cell mutagenicity:

Test: Mutagenesis - Species: Salmonella Typhimurium Negative

Triethanol amine - CAS: 102-71-6

a) acute toxicity:

Test: LD50 - Route: Oral - Species: Guinea pig = 2200 mg/kg - Source: "Toxicometric Parameters of Industrial Toxic Chemicals Under Single Exposure," Izmerov, N.F., et al., Moscow, Centre of International Projects, GKNT, 1982Vol. -, Pg. 114, 1982.

Test: LD50 - Route: Oral - Species: Mouse = 5846 mg/kg - Source: Science Reports of the Research Institutes, Tohoku University, Series C: Medicine. Vol. 36(1-4), Pg. 10, 1989.

If not differently specified, the information required in Regulation (EU) 2015/830 listed below must be considered as 'No data available':

- a) acute toxicity;
- b) skin corrosion/irritation;
- c) serious eye damage/irritation;

Safety Data Sheet

- d) respiratory or skin sensitisation;
- e) germ cell mutagenicity;
- f) carcinogenicity;
- g) reproductive toxicity;
- h) STOT-single exposure;
- i) STOT-repeated exposure;
- j) aspiration hazard.

SECTION 12: Ecological information

12.1. Toxicity

Adopt good working practices, so that the product is not released into the environment.

2,4,7,9-tetramethyldec-5-yne-4,7-diol - CAS: 126-86-3

a) Aquatic acute toxicity:

Endpoint: LC50 - Species: Fish = 36 mg/l - Duration h: 96

Endpoint: EC50 - Species: Daphnia = 88 mg/l - Duration h: 48

Endpoint: EC50 - Species: Algae = 15 mg/l - Duration h: 72

c) Bacteria toxicity:

Endpoint: EC50 - Species: activated sludge = 630 mg/l - Duration h: 0.5

12.2. Persistence and degradability

No data available

12.3. Bioaccumulative potential

No data available

12.4. Mobility in soil

No data available

12.5. Results of PBT and vPvB assessment

vPvB Substances: None - PBT Substances: None

12.6. Other adverse effects

None

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Recover if possible. In so doing, comply with the local and national regulations currently in force.

SECTION 14: Transport information

14.1. UN number

Not classified as dangerous in the meaning of transport regulations.

14.2. UN proper shipping name

No data available

14.3. Transport hazard class(es)

No data available

14.4. Packing group

No data available

14.5. Environmental hazards

No data available

14.6. Special precautions for user

No data available

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

No data available

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Dir. 98/24/EC (Risks related to chemical agents at work)

Dir. 2000/39/EC (Occupational exposure limit values)

Regulation (EC) n. 1907/2006 (REACH)

Regulation (EC) n. 1272/2008 (CLP)

Regulation (EC) n. 790/2009 (ATP 1 CLP) and (EU) n. 758/2013

Regulation (EU) 2015/830

Regulation (EU) n. 286/2011 (ATP 2 CLP)

Regulation (EU) n. 618/2012 (ATP 3 CLP)

Regulation (EU) n. 487/2013 (ATP 4 CLP)

Regulation (EU) n. 944/2013 (ATP 5 CLP)

Regulation (EU) n. 605/2014 (ATP 6 CLP)

Safety Data Sheet

Restrictions related to the product or the substances contained according to Annex XVII Regulation (EC) 1907/2006 (REACH) and subsequent modifications:

Restrictions related to the product:

No restriction.

Restrictions related to the substances contained:

No restriction.

Where applicable, refer to the following regulatory provisions :

Directive 2003/105/CE ('Activities linked to risks of serious accidents') and subsequent amendments.

Regulation (EC) nr 648/2004 (detergents).

1999/13/EC (VOC directive)

Provisions related to directives 82/501/EC(Seveso), 96/82/EC(Seveso II):

No data available

15.2. Chemical safety assessment

No

SECTION 16: Other information

Full text of phrases referred to in Section 3:

H318 Causes serious eye damage.

H412 Harmful to aquatic life with long lasting effects.

H317 May cause an allergic skin reaction.

Hazard class and hazard category	Code	Description
Eye Dam. 1	3.3/1	Serious eye damage, Category 1
Skin Sens. 1B	3.4.2/1B	Skin Sensitisation, Category 1B
Aquatic Chronic 3	4.1/C3	Chronic (long term) aquatic hazard, category 3

This safety data sheet has been completely updated in compliance to Regulation 2015/830.

This document was prepared by a competent person who has received appropriate training.

Main bibliographic sources:

ECDIN - Environmental Chemicals Data and Information Network - Joint Research Centre, Commission of the European Communities

SAX's DANGEROUS PROPERTIES OF INDUSTRIAL MATERIALS - Eight Edition - Van Nostrand Reinold

CCNL - Appendix 1

Ref. 1 ·IARC Monographs on the Evaluation Carcinogenic Risks to Humans (IARC: International Agency for Research on Cancer)

·Journal of Occupational Health (JOH) (Japan Society of Occupational Health (JSOH))

·TLVs and BEIs (ACGIH: American Conference of Governmental Industrial Hygienists)

·IRIS Carcinogenic Assessment (IRIS: Integrated Risk Information System of US EPA)

·National Toxicology Program (NTP) Report on Carcinogens (USA)

·Annex VI of REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT

AND OF THE COUNCIL of 16 December 2008 on classification, labelling and

packaging of substances and mixtures, amending and repealing Directives 67/548/EEC

and 1999/45/EC, and amending Regulation (EC) No 1907/2006

·MAK und BAT Werte Liste (DFG: German Research Foundation)

·TRGS 905, Verzeichnis krebserzeugender, keimzell mutagener oder

reproduktionstoxischer Stoffe (AGS: Committee on Hazardous Substances, Germany)

Ref. 2 ·Annex VI of REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT

AND OF THE COUNCIL of 16 December 2008 on classification, labelling and

packaging of substances and mixtures, amending and repealing Directives 67/548/EEC

and 1999/45/EC, and amending Regulation (EC) No 1907/2006

Safety Data Sheet

-TRGS 905, Verzeichnis krebserzeugender, keimzell mutagener oder reproduktionstoxischer Stoffe (AGS: Committee on Hazardous Substances, Germany)

The information contained herein is based on our state of knowledge at the above-specified date. It refers solely to the product indicated and constitutes no guarantee of particular quality.

It is the duty of the user to ensure that this information is appropriate and complete with respect to the specific use intended.

This Safety Data Sheet cancels and replaces any preceding release.

ADR:	European Agreement concerning the International Carriage of Dangerous Goods by Road.
CAS:	Chemical Abstracts Service (division of the American Chemical Society).
CLP:	Classification, Labeling, Packaging.
DNEL:	Derived No Effect Level.
EINECS:	European Inventory of Existing Commercial Chemical Substances.
GefStoffVO:	Ordinance on Hazardous Substances, Germany.
GHS:	Globally Harmonized System of Classification and Labeling of Chemicals.
IATA:	International Air Transport Association.
IATA-DGR:	Dangerous Goods Regulation by the "International Air Transport Association" (IATA).
ICAO:	International Civil Aviation Organization.
ICAO-TI:	Technical Instructions by the "International Civil Aviation Organization" (ICAO).
IMDG:	International Maritime Code for Dangerous Goods.
INCI:	International Nomenclature of Cosmetic Ingredients.
KSt:	Explosion coefficient.
LC50:	Lethal concentration, for 50 percent of test population.
LD50:	Lethal dose, for 50 percent of test population.
LTE:	Long-term exposure.
PNEC:	Predicted No Effect Concentration.
RID:	Regulation Concerning the International Transport of Dangerous Goods by Rail.
STE:	Short-term exposure.
STEL:	Short Term Exposure limit.
STOT:	Specific Target Organ Toxicity.
TLV:	Threshold Limiting Value.
TWATLV:	Threshold Limit Value for the Time Weighted Average 8 hour day. (ACGIH Standard).
WGK:	German Water Hazard Class.