


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0901301212**
Status: **Active**
Overview: C-Grid III Interconnects
Description: C-Grid III Header, Dual Row, Vertical, Shrouded, Fully Loaded, 12 Circuits, Black, 0.38µm Gold (Au) Selective Plating

Documents:

| | |
|---|--|
| 3D Model | Application Specification 901190001-AS-000 (PDF) |
| Drawing (PDF) | Packaging Specification PK-90130-001-001 (PDF) |
| 3D Model (PDF) | Packaging Specification PK-91814-005-001 (PDF) |
| Product Specification PS-99020-0001-001 (PDF) | RoHS Certificate of Compliance (PDF) |



Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|--------------------------|
| Product Family | PCB Headers |
| Series | 90130 |
| Application | Signal, Wire-to-Board |
| Overview | C-Grid III Interconnects |
| Product Name | C-Grid III |
| UPC | 800753698673 |

Physical

| | |
|--------------------------------|-------------|
| Breakaway | No |
| Circuits (Loaded) | 12 |
| Circuits (maximum) | 12 |
| Color - Resin | Black |
| Durability (mating cycles max) | 100 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | Polyester |
| Net Weight | 1.488/g |
| Number of Rows | 2 |
| Orientation | Vertical |
| PC Tail Length | 2.90mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Tray |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Plating min - Mating | 0.381µm |
| Plating min - Termination | 3.048µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | No |
| Shrouded | Closed Ends |
| Stackable | No |
| Surface Mount Compatible (SMC) | No |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[90130 Series](#)

Mates With

[90142 C-Grid III Crimp Housing](#)

| | |
|-------------------------------|----------------|
| Temperature Range - Operating | -55° to +125°C |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|------------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum | 350V AC/DC |

Solder Process Data

| | |
|--|------|
| Duration at Max. Process Temperature (seconds) | 003 |
| Lead-free Process Capability | WAVE |
| Max. Cycles at Max. Process Temperature | 001 |
| Process Temperature max. C | 235 |

Material Info**Reference - Drawing Numbers**

| | |
|---------------------------|------------------------------------|
| Application Specification | 901190001-AS-000 |
| Packaging Specification | PK-90130-001-001, PK-91814-005-001 |
| Product Specification | PS-99020-0001-001 |
| Sales Drawing | SDA-90130-001 |

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION