

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901512110

Status:

Active

Overview:

C-Grid Connector Products

Description:

C-Grid III PC Board Connector, Dual Row, Vertical, 10 Circuits, Tin (Sn) Plating

Documents:	
3D Model	Application Specification 713080001-AS-000 (PDF)
Drawing (PDF)	Application Specification 901190001-AS-000 (PDF)
3D Model (PDF)	Packaging Specification PK-90151-001-001 (PDF)
Product Specification PS-99020-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E29179
----	--------

General

Product Family	PCB Receptacles
Series	90151
Application	Board-to-Board, Signal
Overview	C-Grid Connector Products
Product Name	C-Grid
UPC	800753672291

Physical


Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Flammability	94HB
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	0.867/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.90mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	3.0A
Grounding to PCB	No
Voltage - Maximum	350V

Solder Process Data

Duration at Max. Process Temperature (seconds)	002
--	-----



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

90151 Series

Mates With

0.64mm square pins

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

Process Temperature max. C

WAVE
001
235

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

713080001-AS-000, 901190001-AS-000
PK-90151-001-001
PS-99020-0001-001
SDA-90151-001

This document was generated on 07/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION