


ADEGAN MANILA SL floor stand

PE rattan anthracite + SST 304 + granite G654, E27, max. 15W

The ADEGAN MANILA floor stand is an elegant and portable outdoor luminaire based on popular rattan materials. Made from granite, stainless steel and PE elements, the luminaire has IP44 protection class. The bulb of choice is protected by a suitable housing in order to achieve this. The ADEGAN MANILA floor luminaire is equipped with a connection lead and an IP plug and supplied ready for direct connection to 230V mains supply.



TECHNICAL DATA

Item no.:	1002494
Socket	E27
Number of sockets	1
Primary nominal voltage	220-240V ~50/60Hz mA/V
Height	175.5 cm
Diameter	38.5 cm
Net weight	16.075 kg
Gross weight	18.162 kg
IP Code	IP 44
Safety class	I
Impact resistance class	IK04
Impact resistance	0,5 Joule
Assembly	Mobile
Wattage	15 W
Color	stainless steel
BIG WHITE Page	554

Recommended lamp

1005289	T38 E27 , white LED light, 8W 3000K CRI90 240°
1005307	T45 E27 , white LED light, 13.5W 3000K CRI90 240°