

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0739447216

Status:


Active

Overview:

HDM Backplane Connector System

Description:

HDM Board-to-Board Backplane Header, Vertical, SMC, Solder Tail, Guide Pin Option, Guide Post Location B, Polarizing Key Position N/A, 144 Circuits



|                |                                                 |
|----------------|-------------------------------------------------|
| Documents:     |                                                 |
| 3D Model       | Product Specification PS-73670-9999-001 (PDF)   |
| 3D Model (PDF) | Packaging Specification PK-70873-0818-001 (PDF) |
| Drawing (PDF)  | RoHS Certificate of Compliance (PDF)            |

|                                |                                  |
|--------------------------------|----------------------------------|
| Agency Certification           |                                  |
| CSA                            | LR19980                          |
| UL                             | E29179                           |
| General                        |                                  |
| Product Family                 | Backplane Connectors             |
| Series                         | 73944                            |
| Application                    | Backplane                        |
| Component Type                 | PCB Header                       |
| Overview                       | HDM Backplane Connector System   |
| Product Name                   | HDM                              |
| UPC                            | 800754876551                     |
| Physical                       |                                  |
| Circuits (Loaded)              | 144                              |
| Circuits (maximum)             | 144                              |
| Color - Resin                  | Black, Natural                   |
| Durability (mating cycles max) | 250                              |
| First Mate / Last Break        | No                               |
| Flammability                   | 94V-0                            |
| Guide to Mating Part           | Yes                              |
| Keying to Mating Part          | Yes                              |
| Material - Metal               | Phosphor Bronze, Stainless Steel |
| Material - Plating Mating      | Gold                             |
| Material - Plating Termination | Tin                              |
| Material - Resin               | High Temperature Thermoplastic   |
| Net Weight                     | 8.594/g                          |
| Number of Columns              | 24                               |
| Number of Pairs                | Open Pin Field                   |
| Number of Rows                 | 6                                |
| Orientation                    | Vertical                         |
| PC Tail Length                 | 3.50mm                           |
| PCB Locator                    | Yes                              |
| PCB Retention                  | None                             |
| PCB Thickness - Recommended    | 2.50mm                           |
| Packaging Type                 | Tube                             |
| Pitch - Mating Interface       | 2.00mm                           |
| Pitch - Termination Interface  | 2.00mm                           |
| Plating min - Mating           | 0.762µm                          |
| Plating min - Termination      | 2.540µm                          |
| Polarized to PCB               | No                               |
| Stackable                      | No                               |
| Surface Mount Compatible (SMC) | No                               |
| Temperature Range - Operating  | -55° to +105°C                   |
| Termination Interface: Style   | Through Hole                     |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2020)9139-DC (19 Jan 2021)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

73944 Series

Mates With

73632 HDM+ Board-to-Board Daughtercard Receptacle. 73780 HDM Board-to-Board Daughtercard Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

|                 |           |
|-----------------|-----------|
| Description     | Product # |
| Extraction Tool | 621001000 |

**Electrical**

|                               |          |
|-------------------------------|----------|
| Current - Maximum per Contact | 1.0A     |
| Data Rate                     | 1.0 Gbps |
| Shielded                      | No       |
| Voltage - Maximum             | 250V AC  |

**Material Info**

**Reference - Drawing Numbers**

|                         |                                    |
|-------------------------|------------------------------------|
| Packaging Specification | PK-70873-0818-001                  |
| Product Specification   | PS-73670-9999-001                  |
| Sales Drawing           | SD-73944-001-001, SD-73944-001-002 |

This document was generated on 10/06/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**