SUBJECT: SCOPE OF DOCUMENT

CONTAINS:

- 1-0. General Description
- 2-0. Input Requirements
- 3-0. Output Requirements
- 4-0. Reliability
- 5-0. Environment
- 6-0. Safety
- 7-0. Mechanical Characteristics

1-0. General Description

The purpose of the document is to specify a Single phase AC input, single output switching power supply. This specification is suitable for: EA10442G Series This product is AC to DC switching power transfer device, it can provide for a 24V, 1.66A max & 40W max DC output with constant voltage source. This Specification defines the input, output, performance characteristics, environment, noise and safety requirement for a power supply.

2-0. Input Requirements

2-1. Input Voltage

Rated Voltage 100-240 Vac +/- 10% full range. Normal line input 115Vac/60Hz, 230Vac/50Hz.

2-2. Input Frequency

47~63 Hz

2-3. Input Current

- a. 1.0A(Max.) @ 115Vac input with full load.
- b. 0.75A(Max.) @ 230Vac input with full load.

2-4. Energy saving standards:

2-4-0. Designed to meet the following standard:

CoC Tier2

2-4-1.Efficiency

Efficiency 88.58% (avg.) normal input & 25%, 50%, 75%, 100% of max output load 2-4-2 No Load Power Consumption.

No Load Watt 0.075W at normal line input.

2-5. Configuration

2-wire AC input (Line, Neutral)

2-6. Input Fuse

The hot line side of the input shall have a fuse, rating (3.15A/250V)

2-7. Inrush Current

70A at 110 Vac At cold start, maximum load.140A at 240 Vac At cold start, maximum load.

2-8. Line Regulation

This line regulation is less than ± 1%, of rated output voltage @ full load

2-9. Hold Up Time

8.3 mSec., @ Normal line, with full load.

2-10. Rise Time

50 mSec.,@ 100-240VAC input, with full load from 10% to 90% of output voltage.

2-11. Turn-ON Time

The output voltage should rise to 90% of rated output voltage in less than 3 SEC. from AC apply to 110Vac start up.

3-0. Output Requirements

3-1. Output Voltage and Current

Output Voltage (Vdc)	Current Min.(A)	Current Max.(A)		
+24V	0	1.66A		

3-2. Load Regulation

Voltage (Vdc)	Tolerance (%)		
+24V	+5/, -5		

3-3. Dynamic Load Regulation

 \pm 5% excursion for 50% - 100% or 100% - 50% load change of DC output at any frequency up to 1KHz(duty 50%)

3-4. Ripple & Noise

The power supply shall not exceed the following limits on the indicated voltage for 60Hz or 50Hz ripple, Switching frequency ripple and noise and dynamic load variations measured with a 20MHz bandwidth

Output	Ripple/Noise			
+24V	1.5% max. of rated output voltage			

Input condition: for rated voltage, Output condition: for max load

Ripple / Noise: 60Hz ripple + switching ripple and noise

Ripple & Noise are measured at the end of output cable which are added a 0.1uF ceramic capacitor and a 47uF electrolytic capacitor

3-5. Over Voltage Protection

180% Max. of rated voltage.

The output voltage shall be shutdown and latch-off when OVP occurred.

3-6. Over Current Protection

110%-200% of rated output current.

The adapter will enter protection at overload mode and no damage.

It will enter into normal condition if the fault condition is removed.

3-7. Stability

2% Max. at constant load with constant input (after 30 minutes of operation).

3-8.Temperature Rise

Less than 45 on top/bottom case at normal AC input & 80% load of DC output at environment temperature 25 .

3-9. Drop-out (Power Line Disturbance)

Output voltage shall remain within the specified regulation range, through the absence of a line input during 1/2 cycle, at full load and normal AC line input

3-10. Voltage Isolation

The DC ground will be isolated from the AC neutral and AC line.

4-0.Reliability

4-1. MTBF (MIL-HDBK-217F)

The power supply shall be designed and produced to have a mean time between failure (MTBF) of 100,000 hours at 25 degrees C.

5-0. Environment

5-1 Temperature

a. Operating: 0 to 40 b. Storage: -20 to 85

5-2 Humidity

a. Operating : 10 to 90 %b. Storage: 5 to 90 %

5-3 Altitude

From sea level to 5,000 Meter (operation) and 5,000 Meter (non operation)

6-0. Safety

6-1. Hi-Pot Test

P->S: 3000Vac 2Sec 10mA;

6-2. Insulation Test

500Vdc, 2Sec. between primary and secondary circuit IR should 100 M .

6-3. Leakage Current

250uA at 240Vac/50 Hz

6-4. Safety

UL, CUL, TUV, CB, CE, FCC, BSMI, CU, RCM, IRAM, CU

6-5. EMS

Items	Specification	Reference	
ECD	Contact: ± 4KV	IEC 61000-4-2	
ESD	Air: ± 8KV	TEC 01000-4-2	
RS	Frequency: 80~1000MHz Field Strength: 3V/M , 80% AM(1KHz)	IEC 61000-4-3	
EFT	1.0 KV on input AC power ports.	IEC 61000-4-4	
SURGE	Line to Line: ± 1KV (peak)	IEC 61000-4-5	

6-6. EMI

Comply with Standards					
CISPR 32, EN 55032 Class B					
FCC PART 15 Class B					

7-0. Mechanical Characteristics

7-1. Physical Size: 85.5 L x 35.7 W x 25.7 H (mm)

7-2. Enclosure material: 94V-0 minimum

7-3. Output Cable (Reference): UL1185 #16


7-4. Vibration Test


The vibration frequencies are set at 20Hz, with total amplitude of 1.5mm Along the 3 directions namely X-Y-Z. The each direction should be vibrated for 60 minutes, after testing no abnormal electrical or mechanical should occur.


7-5. Drop Test (Referencing to CSA C22.2 No.950/UL1950/UL1310/EN62368)


Products shall be dropped from a height of 1000 mm onto a horizontal surface consists of hardwood at 13mm thick, mounted on two layers of plywood each 19mm to 20mm thick, all supported on a concrete or equivalent non-resilient floor. Upon conclusion of test, the equipment cannot into hazardous moving parts and hazardous voltage circuits need be operational, and need meet Hi-Pot 19mm to 20mm thick, all supported on a concrete or equivalent non-resilient

7-6. Net Weight (Reference):160g









E	APPROVED			
MODEL	EA10442G(T01)	UNIT	mm	DESIGNED
color	BLACK	SCALE		CHECK
cus.		DATE	2020-05-15	DRAWING

EDAC EDACPOWER ELEC.

AC ADAPTER 电源适配器 電源供應器

MODEL 型号型號:EA10442G-240 AC INPUT 输入輸入:100-240Vac, 1.0A, 50-60Hz

DC OUTPUT 输出输出:24.0V===1.66A 40.0W

CAUTION 注意 注意

FOR INDOOR USE ONLY 室內产品使用 室內產品使用

I.T.E. USE ONLY

DATE CODE:

出厂日期 出廠日期

20	21	22			1	2	3	4	5
1	2	3	4	5	6	7	8	9	0

13128







I.T.E. POWER SUPPLY

E209833 LPS















制造商:翌胜电子股份有限公司

C1 C3 MADE IN CHINA 中国制造 中國製造

EDAC LABEL P/N.: 3128

Background: Black color

Character: Silver color

Unit: mm