LogiLink_®

Magnifying Desk Glass Lamp 3/12 Diopter

Art. No.: **WZ0059**



LED

Lumens



Glass Lens

Enlargement





Specifications:

Power	AC 230V, 50 Hz
LED Type	SMD LED
LED Quantity	6,5 W/40 PCS
Energy Usage Consumption	6,5 kwh/1000 h
EEK (Energy Efficiency Class)	F
Color Temperature	6500 K
Luminous Flux	520 lm
CRI (Color Rendering Index)	80 Ra
Flicker Metric	0,007 W
Stroboscopic Effect Metric	0,013 W
Power Usage	6,5 W
Lifetime	20000 hours
Lens Material	Glass
Lens Size	4 inch
Operating Temperature	0–30 °C
Operating Humidity	0–65% RH (no condensation)
Storage Temperature	-10-40 °C
Storage Humidity	0–65% RH (no condensation)
Housing Material	Plastic
Cable length	1,5 m
Dimensions	28x23x19 cm
Weight	1,1 kg

Package Contents:

- » 1x Magnifying Glass Lamp
- » 1x Allen Wrench
- » 1x User Manual

Package Information:

- » Packing Dimension: 280x230x190 mm
- » Packing Weight: 1,7 kg
- » Carton Dimension: 580x480x405 mm
- » Carton Q'ty: 8 pcs» Carton Weight: 15,5 kg











