

Product data sheet

Automation technology - sensors and actuators



Product description	M12-A connection cable male cable connector - female cable connector, Contacts: 5, unshielded, moulded cable, IP69K, UL, PUR black, 5 x 0.34 mm ² , 3 m
Area	M12-A series 763
Part no.	77 3430 3429 50005-0300

Material

Contact body material	PUR
Contact material	CuZn (brass)
Contact plating	Au (gold)
REACH SVHC	None (No pollutants)
SCIP number	SCIP-number not available

Authorization/approvals

Approvals	UL
-----------	----

Cable data - Structure of the cable

Cable diameter	5.0 mm
Cross section	5 x 0.34 mm ²
Sheath material	PUR
Single-lead insulation	PP9Y halogen-free
Single-lead structure	42 x 0.10 mm
Cable color	black

Cable data - Mechanical properties

Bending radius, fixed cable	≥ 5 x Ø
Bending radius, moving cable	≥ 10 x Ø
Bending cycles	>5 million
Permitted acceleration	5 m/s ²
Travel speed	≤ 200 m/min (5 m horizontal distance)

Cable data - Thermal properties

Temperature range cable in move from/to	-25 °C / 90 °C
Temperature range cable fixed from/to	-50 °C / 90 °C

Product description	M12-A connection cable male cable connector - female cable connector, Contacts: 5, unshielded, moulded cable, IP69K, UL, PUR black, 5 x 0.34 mm ² , 3 m
Area	M12-A series 763
Part no.	77 3430 3429 50005-0300

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP 67 and IP 68 are not suitable for use under water. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).