





3000±100MM



PIN OUT



NOTE:

- ELECTRICAL TEST:100% OPEN SHORT, MISS WIRE TEST
- TEST LIMIT:ISO11801 Channel Class E
- Working temperature:-10°C ~ + 60°C
- Plug Contacts durability:750 cycles min
- RoHS2.0 AND REACH compliant
- Spray WORD:  
CAT.6 S/FTP 27AWG 250MHz LSZH PATCH CORD ISO/IEC 11801 & EN50173 & TIA/EIA 568.2-D
- Dielectric strength: DC 1.0KV for 1min or 2.5KV for 2s  
AC 0.7KV for 1min or 1.7KV for 2s
- Packing:: Bandrole with Euro hole w/RENKFORCE sticker

MATERIAL LIST

③	CABLE	CAT.6 S/FTP 27AWG(BC*1P+AL-FOIL)*4+BRAID AL-MG JACKET:LSZH OD:6.0±0.2mm Black (Pantone black 3C)	1	
②	Over mold	PVC 75A Black (Pantone black 3C)	2	
①	Plug	RJ45 8P8C'S SHIELDED ,THE SHELL PLATED NICKEL, PIN GOLD PLATED 3u" RED/TRANSPARENT	2	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

Renkforce					
CUSTOMER NO.	CN	BN.	2489871		
PRODUCT NAME	Cat.6 S/FTP Round Patch cord 27AWG			UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE		
Hasia	ARVIN		2022-12-21		