

KERN OBN 159

KERN

Professionalism and versatility united in one microscope – with Koehler illumination for demanding applications



Category

Brand	Optics
Product category	Microscope
Product group	Compound microscope
Product family	OBN-15

Construction

Dimension (W×D×H)	390×200×400 mm
Optical system	Infinity
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Tube type	Siedentopf
Light distribution	0:100 80:20

Contrasting methods	Bright field Darkfield (optional) Phase contrast Polarisation (optional) Fluorescent (optinal)
---------------------	--

Standard objectives	4× PH 10× PH 20× PH 40× PH 100×
---------------------	---

Lens quality	Infinity Plan
Nosepiece screw-in locations	5
Interpupillary distance [Min]	50 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5

Ocular

Ocular type	Eyeiece HWF 10x / Ø 20mm with anti-fungus, high eye point
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	20 mm
Ocular diameter	23,2 mm

Objective

Objectives - Details	PH-Objective Infinity Plan 10x / 0,25 anti-fungus PH-Objective Infinity Plan 100x / 1,25 oil, anti-fungus PH-Objective Infinity Plan 20x / 0,4 spring, anti-fungus Objective Infinity Plan 4x / 0,11 anti-fungus PH-Objective Infinity Plan 40x / 0,66 spring, anti-fungus
----------------------	--

Objectives magnifications	4x / 10x / 20x / 40x / 100x
---------------------------	-----------------------------

Illumination

Illuminance	Transmitted light
Illumination type transmitted light	LED
Illumination intensity transmitted light	3 W
Illumination dimmable	Transmitted light
Koehler illumination	✓
Filter possible	✓
Phase-contrast unit	Quintuple condenser wheel
Aperture diaphragm	✓
Field diaphragm	✓

Focussing

Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

KERN OBN 159



Professionalism and versatility united in one microscope – with Koehler illumination for demanding applications

Condensor

Condensor type	PH universal rotary condenser
----------------	-------------------------------

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter

Plug-in power supply / adapter for countries - included with the delivery	EURO
---	------

Plug-in power supply / adapter for countries - optional	AUS UK US CH
---	-----------------------

Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
--	---------------------------------

Power supply cable removable	removable
------------------------------	-----------

Input voltage device / power [Max]	5 V, 1 A
------------------------------------	----------

Environmental conditions

Storage temperature [Min]	-5 °C
---------------------------	-------

Storage temperature [Max]	40 °C
---------------------------	-------

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	535×370×270 mm
------------------------------	----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	10 kg
--------------------	-------

Gross weight approx.	11 kg
----------------------	-------

Shipping weight	11 kg
-----------------	-------

Product information

GTIN/EAN number	4045761267824
-----------------	---------------

REACH classification	no prohibited substances
----------------------	--------------------------

Pictograms

STANDARD



OPTION

