

# EE-SX1105

## Compact Slot/Terminal Type (Slot Width: 2 mm)

- Low profile (Height: 3.3 mm) type
- Terminal for PCB mounting




Be sure to read *Safety Precautions* on Page 3.

RoHS Compliant

## Ordering Information

### Photomicrosensor

Appearance	Sensing method	Connecting method	Sensing distance	Aperture size (H × W) (mm)	Output type	Model	Minimum packing unit (Unit: pcs)
	Transmissive (slot type)	Terminal for PCB mounting	2 mm (Slot width)	Both emitting side and detecting side 1 × 0.4	Phototransistor	EE-SX1105	1

Note: Order in multiples of minimum packing unit.

## Ratings, Characteristics and Exterior Specifications

### Absolute Maximum Ratings (Ta = 25°C)

Item	Symbol	Rated value	Unit
<b>Emitter</b>			
Forward current	$I_F$	50*1	mA
Pulse forward current	$I_{FP}$	—	A
Reverse voltage	$V_R$	5	V
<b>Detector</b>			
Collector-Emitter voltage	$V_{CE0}$	30	V
Emitter-Collector voltage	$V_{ECO}$	4.5	V
Collector current	$I_C$	30	mA
Collector dissipation	$P_C$	80*1	mW
Operating temperature	$T_{opr}$	-25 to 85	°C
Storage temperature	$T_{stg}$	-30 to 85	°C
Soldering temperature	$T_{sol}$	260*2	°C

\*1. Refer to the temperature rating chart if the ambient temperature exceeds 25°C.

\*2. Complete soldering within 3 seconds.

### Exterior Specifications


Connecting method	Weight (g)	Material	
		Case	Lens
Terminal for PCB mounting	0.1	PPS	Epoxy resin

### Electrical and Optical Characteristics (Ta = 25°C)


Item	Symbol	Value			Unit	Condition
		MIN.	TYP.	MAX.		
<b>Emitter</b>						
Forward voltage	$V_F$	—	1.3	1.6	V	$I_F = 50$ mA
Reverse current	$I_R$	—	—	10	μA	$V_R = 5$ V
Peak emission wavelength	$\lambda_P$	—	950	—	nm	$I_F = 50$ mA
<b>Detector</b>						
Light current	$I_L$	0.2	—	—	mA	$I_F = 20$ mA, $V_{CE} = 5$ V
Dark current	$I_D$	—	—	500	nA	$V_{CE} = 10$ V, 0 lx
Leakage current	$I_{LEAK}$	—	—	—	μA	—
Collector-Emitter saturated voltage	$V_{CE(sat)}$	—	—	0.4	V	$I_F = 20$ mA, $I_L = 0.1$ mA
Peak spectral sensitivity wavelength	$\lambda_P$	—	800	—	nm	$V_{CE} = 5$ V
Rising time	$t_r$	—	10	—	μs	$V_{CC} = 5$ V, $R_L = 100$ Ω, $I_F = 20$ mA
Falling time	$t_f$	—	10	—	μs	$V_{CC} = 5$ V, $R_L = 100$ Ω, $I_F = 20$ mA

# Engineering Data (Reference Value)


**Fig 1. Forward Current vs. Collector Dissipation Temperature Rating**




**Fig 2. Forward Current vs. Forward Voltage Characteristics (Typical)**




**Fig 3. Light Current vs. Forward Current Characteristics (Typical)**




**Fig 4. Light Current vs. Collector-Emitter Voltage Characteristics (Typical)**




**Fig 5. Relative Light Current vs. Ambient Temperature Characteristics (Typical)**




**Fig 6. Dark Current vs. Ambient Temperature Characteristics (Typical)**




**Fig 7. Response Time vs. Light Current Characteristics (Typical)**




**Fig 8. Sensing Position Characteristics (Typical)**



**Fig 9. Sensing Position Characteristics (Typical)**



**Fig 10. Response Time Measurement Circuit**



# Safety Precautions

To ensure safe operation, be sure to read and follow the Instruction Manual provided with the Sensor.

**⚠ CAUTION**

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.

**Precautions for Correct Use**

Do not use the product in atmospheres or environments that exceed product ratings.

**Precautions for Safe Use**

**Do not use the product with a voltage or current that exceeds the rated range.**  
Applying a voltage or current that is higher than the rated range may result in explosion or fire.

**Do not miswire such as the polarity of the power supply voltage.**  
Otherwise the product may be damaged or it may burn.


**This product does not resist water. Do not use the product in places where water or oil may be sprayed onto the product.**

## Dimensions and Internal Circuit

(Unit: mm)


### Photomicrosensor

EE-SX1105




Aperture size (H × W)

Emitter	Detector
1 × 0.4	1 × 0.4



Internal circuit



Terminal No.	Name
A	Anode
K	Cathode
C	Collector
E	Emitter

**Note:** 1. Unless otherwise specified, the tolerances are ±0.2 mm.  
 2. Dimensions in parentheses are for reference only.  
 3. Dimensions of the slit are those of the primary mold.