



Discover more details and matching accessories online!

User-friendly hanging scale for rapid, mobile weighing

Features

- **1** With the TÜV certification mark, the scales meet the requirements of the standard EN 13155 (Non-fixed load lifting attachments/ Breakage resistance) and EN 61010-1 (Electrical safety)
- HDB-XL: High-capacity XL-version. The larger design creates space for a large handle, which enables even better handling especially with heavier loads
- Ideal for rapid control in goods-in and goods-out
- Also essential in the private sector to determine the weight of fish, game, fruits, bicycle parts, suitcases etc.
- Hold function: For easy reading of the weighing result, the display can be „frozen“ in different ways. Either automatically when the weighing value remains unchanged or manually by pressing the Hold key
- Hook, steel, included with the delivery. Can be hinged on HDB-N models
- Peak load display (peak hold)

Technical data

- LCD display, digit height 12 mm
- Ready for use: Batteries included, 2×1.5 V AAA, operating time up to 100 h
- Weighing units: kg, lb, N
- Permissible ambient temperature 5 °C/35 °C

STANDARD



OPTION



Model	Weighing capacity	Readability	Dimensions	Net weight	Options
					Calibr. Certificate
KERN	[Max] kg	[d] g	W×D×H mm	approx. kg	DAkkS accr. KERN
HDB 5K5N	5	5	72×25×188	0,20	963-127H
HDB 10K10N	10	10	72×25×188	0,20	963-128H
High-capacity XL-version					
HDB 10K-2XL	15	10	101×25×203	0,25	963-128H
HDB 30K-2XL	30	20	101×25×211	0,25	963-128H