

Type : Mercury and Lead Free Button Cell

Chemical System : Zinc/Manganese Dioxide

Nominal Voltage : 1.5V

Nominal Dimension : $\Phi 7.9 \times 3.6$ mm

Applications : Watch(with alarm and lamp), calculator, electronic toys melody card, ...etc.

Average Weight : 0.5g

Date Code : Unless otherwise specified, each cell will carry a numeric year code and an alphabetical month code.

Close Circuit Voltage : 1.3V(min.)(load resistor 200 Ω at 20 $^{\circ}$ C for 0.1 to 2 seconds)


Nominal Service Life : 116hrs (load 6.2k Ω to cut off 1.0V under 20 $^{\circ}$ C)

Average Service Capacity : 24mAh (load 6.2 Ω to cut off 1.0V under 20 $^{\circ}$ C)


Cross References:

IEC	JIS	Eveready	Varta
LR41	LR41	192	V3GA

Model No.: GP192F



Typical Discharge Curve at 20 $^{\circ}$ C



The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.