

Description : Mercury and Lead Free Button Cell

Chemical system : Zinc-Manganese Dioxide

Nominal voltage : 1.5Volts

Nominal capacity : 30mAh

Dimensions : Ø7.9mm x 3.6mm


Average weight : 0.5 grams

Operation temperature: 0°C - 45°C

Storage temperature : 10°C ~25°C

Shelf life : 3 years at room temperature

Model no.: GP192F




Unit : mm

Cross References:

IEC	JIS	ANSI	Varta
LR41	AG3	392A	LR41

Discharge Characteristics

Typical discharge characteristics at 20°C / 55% r.h.:



Ultra+
LITHIUM

The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

gpbatteries.com

Manufacturer reserves the right to alter or amend the design, model and specification with out prior notice.
Copyright© GP Batteries International Limited - All rights reserved

Member
Gold Peak Group

202103