



## New Cosy+ Range

Pick up the right Internet Connectivity

### Ewon Cosy+ ETH

The Ewon Cosy+ is an industrial VPN gateway designed to offer secure remote access across the Internet, to machines and equipment at customers' sites or in the field.



### Key Benefits

<p><b>EASIER THAN EASY</b></p>	<p>Straightforward setup, to make any machine IIoT-ready in a matter of minutes.          Non-intrusive outbound connections, requiring no change on the existing network.          Reach your equipment in 2 clicks, wherever it is.</p>
<p><b>NO HIDDEN COSTS</b></p>	<p>Start immediately with a free Talk2M account, supporting an unlimited number of devices and users.          Connect from any device, with the free desktop, web and mobile apps.</p>
<p><b>IT APPROVED</b></p>	<p>Trusted chain from Hardware to the Cloud:</p> <ul style="list-style-type: none"> <li>• Hardware Root Of Trust brings security to the core of the hardware.</li> <li>• Secure Element, the perfect place to store crucial secrets.</li> <li>• Birth certificate to prevents cloning and counterfeiting.</li> <li>• Secure boot sequence ensuring that only code signed by Ewon is executed.</li> <li>• Restrictive list of most secured cypher suites to protect the communications with Talk2M.</li> </ul> <p>Proven security posture:</p> <ul style="list-style-type: none"> <li>• Certified ISO 27001 &amp; cybersecurity partnership with NVDISO.</li> <li>• Solution based on the latest open standard technologies.</li> </ul> <p>Manage the connectivity of all your machines and collaborators from one place.</p>
<p><b>READY TO USE AND RELIABLE</b></p>	<p>20+ data centers spread worldwide for coverage and maximal business continuity.          Global and reliable infrastructure, with an extensive Service Level Agreement.          Scalability: add at any time as many devices and users as you need.          Email &amp; SMS relay services, to receive notifications from your machine.</p>

### PLC Connectivity

Remote access possibilities:

Using the Ewon Cosy, you can remotely connect to your PLC using its Ethernet port or its USB interface.

USB device support depends on the compatibility between the USB driver used on the PC and the Talk2M USB integration.

In principle, all PLC models with an Ethernet port are supported.

Below is a non-exhaustive list of some of the compatible devices for major PLC brands:

<b>Rockwell Automation/Allen Bradley</b>	SLC5/500 Series (over Eth) Micro/Compact/Control Logix Series (over Eth/USB)
<b>Siemens</b>	S7-200/300/400/1200/1500 (over Eth)* Logo (over Eth)
<b>Schneider Electric</b>	TSX Series (over Eth) M Series (M258, M340, ...) (over Eth/USB)
<b>Mitsubishi Electric</b>	iQ-R, iQ-F series (over Eth) Q, F, L series (over Eth)
<b>VIPA</b>	Speed 7 series (over Eth)
<b>OMRON</b>	C, CJ, CP, CS Series (over Eth/USB) NJ, NX Series (over Eth/USB)
<b>HITACHI</b>	EH Series
<b>KEYENCE</b>	KV series
<b>Yokogawa</b>	e-RT3 series, FA-M3V series

\*remote access to safety PLC devices (-F series) is not supported

## Technical Specifications

<b>WAN Ethernet</b>	up to 3 ports, 10/100 Mb Ethernet.
<b>LAN Ethernet</b>	up to 4 ports, 10/100 Mb Ethernet.
<b>Field interface</b>	Up to 10 USB 2.0 connections, female connector 2.0.
<b>SD Card reader</b>	YES, for Cosy commissioning (firmware upgrade, backup, Talk2M registration).
<b>Router</b>	IP filtering, IP forwarding, NAT, Port forwarding, Proxy, Routing table, DHCP client/server.
<b>Internet</b>	Outbound connection for Talk2M through port TCP 443 (and optionally port UDP 1194).
<b>VPN Tunneling</b>	OpenVPN either in SSL UDP or TCP.
<b>Talk2M</b>	Talk2M Free+ or Talk2M Pro, natively supported.
<b>VPN Security</b>	Communications between the remote user and the Ewon gateway are fully encrypted using the SSL/TLS protocol, thereby ensuring data authenticity, integrity & confidentiality. All users and Ewon units are authenticated using x509 SSL certificates and end-to-end traffic is encrypted using strong symmetric & asymmetric algorithms that are part of the SSL/TLS protocol cipher suite.
<b>Synchronization</b>	Embedded real-time clock, manual setup via the web interface or automatic via NTP.
<b>File Management</b>	FTP server for configuration, firmware update.
<b>Web-based configuration</b>	Embedded web interface with setup wizards for configuration and maintenance (no additional software needed). Basic authentication (login/password) and session control for security.
<b>Mechanicals</b>	Dimensions: 108,80 x 99 x 43,60 mm (H x D x W).

	DIN rail or wall screw fixing system.
<b>Weight</b>	198 gr.
<b>Power supply</b>	12-24 VDC +/-20%, LPS.
<b>Temperature Range</b>	Operating: -25°C to +60°C, 10 to 95% relative humidity (non-condensing). Storage: -30°C to +70°C, 10 to 95% relative humidity (non-condensing).
<b>Hardware</b>	1xDO: open drain ( MOSFET) 200mA; isolation 1.5kV, 2xDI: 0 to 24VDC; 1.5 kV isolation.
<b>Marking</b>	CE, cULus, FCC, CAN ICES-3(B)/NMS-3(B), UKCA
<b>Warranty</b>	36 months

## Certifications

<b>Type tests</b>	Temperature - Operating & Storage tested according to: IEC 60068-2-1 Cold test IEC 60068-2-2 Dry heat test IEC 60068-2-14 Change of temperature IEC 60068-2-30 Cyclic damp heat test Vibration & shocks tested according to: IEC 60068-2-27 Bumps IEC 60068-2-64 Vibration (broad-band random) IEC 60068-2-6 Vibration (sinusoidal)
<b>CE</b>	Compliant with: EMC directive 2014/30/EU (Immunity: industrial level) ROHS2 2011/65/EU directive with amendment 2015/863 REACH regulation
<b>UKCA</b>	Compliant with: Electromagnetic Compatibility Regulations 2016; The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012.
<b>FCC/IC</b>	This product complies with the Part 15 of the FCC rules.
<b>Japan</b>	This device complies with Japanese regulations.
<b>Safety</b>	The product fulfils the requirements of: EN 62368-1:2014 + A11:2017 UI 62368-1 Second Edition CAN/CSA C22.2 No. 62368-1-14 Second Edition

## Ordering Information

**ORDER CODE: EC71330\_00MA**

**MODEL NUMBER: 01702**

**WARRANTY:** 3 years

For purchasing instructions and terms and conditions, see: → [How to buy](#)

Do you want the advice of our experts? → [Contact Us](#)

# Cosy131 Range

Pick up the right Internet Connectivity



Ewon Cosy 131 -  
ETH

Wired Ethernet  
WAN connectivity



Ewon Cosy 131 -  
WiFi

WiFi connectivity on  
2.4Ghz networks



Ewon Cosy 131 - 4G  
EU

4G Cellular  
connectivity for  
Europe



Ewon Cosy 131 - 4G  
NA

4G Cellular  
connectivity for  
United States and  
Canada



Ewon Cosy 131 - 4G  
APAC

4G Cellular  
connectivity for  
Asia-Pacific  
countries



Ewon Cosy 131 - 3G

3G Worldwide  
cellular connectivity