

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

LITHIUM CAMERA BATTERY 650 MAH



Item no.: 2542799

TECHNICAL DATA

Type	Li-ion CR123
Classification	Rechargeable
Nominal voltage	3.0 V
Capacity	650 mAh
Rated energy	1.95 Wh
Environment temperature	General: 20 °C ± 5 °C Charging: 0 to +45 °C Discharging: -20 to +60 °C Storage: - (≤1 month) -20 to +55 °C - (≤3 month) -20 to +45 °C - (≤12 months) -5 to +30 °C
Environment humidity	45 - 85 % RH
Environment atmospheric pressure	86 - 106 kPa
Dimensions (H x Ø)	34.6 x 16.3 mm
Weight (approx.)	18 g per pc


*For performance and safety, observe the operating / storage conditions.

PERFORMANCE CHARACTERISTICS

Charge/discharge curves



DIMENSIONS



All dimensions in mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.

*2542799_V1_0326_02_dm_ds_en