

DATASHEET

Item No.: 2542815

Type designation: ML2032

Chemical system: Manganese lithium


Nominal voltage: 3.0 V


Weight: Approximate 3.2 g

Dimension (mm): Ø20* 3.2

The dimensions shall be in accordance with the below figures both prior to and after the service output test.

Measuring equipment shall be with a minimum accuracy of +0.1/-0.2 mm.





Capacity: 65 mAh (15k Ω load to 2.0 V end-point)

Operating temperature: -20 $^{\circ}\mathrm{C}$ ~ 70 $^{\circ}\mathrm{C}$

Recommend storage temperature: 0 °C ~ 30 °C

Shelf lifetime: 1 Year

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright by Conrad Electronic SE.

2542815_v1_1222_voltcraft_ds