

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

UC-2C1A65W01 65 W GaN Charger

CE

Item no: 2559644

The product is a GaN charger with fast charge support.

FEATURES

USB-C® x 2 // USB-A x 1 // Fast charge with PD3.0 support // Max. 65W



TECHNICAL DATA

Data according to EU regulation 2019/1782

Manufacturer	Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau
Commercial registration number	HRB 3896
Model identifier	UC-2C1A65W01
Input voltage	100 - 240 V/AC
Input AC frequency	50 / 60 Hz
Output voltage Output current Output power	USB C1: 5.0 V 3.0 A, 9.0 V 3.0 A, 12.0 V 3.0 A, 15.0 V 3.0 A, 20.0 V 3.25 A max. 65.0 W USB C2: 5.0 V 3.0 A, 9.0 V 2.22 A, 12.0 V 1.67 A, max. 20.0 W USB-A: 5.0 V 3.0 A , 9.0 V 2.0 A, 12.0 V 1.5 A, max. 18.0 W USB-C1+USB-C2: 45.0 W + 20.0 W (65.0 W max.) USB-C1+USB-A: 45.0 W+18.0 W (63.0 W max.) USB-C2+USB-A 5.0 V/DC 3.0 A (15.0 W max.) USB-C1+USB-C2+USB-A 45.0 W+15.0 W (60.0 W max.)
Average active efficiency	90.0 %
Efficiency at low load (10 %)	82.0 %
No-load power consumption	0.02W

Environment

Operating conditions	0 to +45 °C, 5 - 90 % RH (non-condensing)
Storage conditions	-35 to +70 °C, 0 - 90 % RH (non-condensing)

Others

Dimensions (W x H x D) (approx.)	approx. 29 x 66 x 41 mm
Weight (approx.)	109 g

CONTENTS

Product // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*2559644_V1_0125_en_ds 1866830091 I1/O1 en