


Automation Technology - Voltage and Power Supply

Product description	7/8" connection cable male cable connector - female cable connector, Contacts: 4, unshielded, moulded cable, IP68, UL, PUR black, 4 x 1.50 mm ² , 10 m
Area	7/8" series 870
Part no.	77 1430 1429 50004-1000


Illustration



Scale drawing



Contact arrangement (Plug-in side)



Technical data

General features

Part no.	77 1430 1429 50004-1000
Connector design	connection cable male cable connector - female cable connector
Cable length	10 m
Version	connecting cable
Connector locking system	screw
Termination	moulded cable
Degree of protection	IP68
Cross-sectional area	1.50 mm ² / AWG 16
Temperature range from/to	-25 °C / 80 °C
Mechanical operation	> 100 Mating cycles
Weight (g)	282.00
Customs tariff number	85444290

Electrical parameters

Rated voltage	300 V (600 V UL)
Rated impulse voltage	2500 V
Rated current (40 °C)	10,0 A
Insulation resistance	> 10 ⁸ Ω
Pollution degree	3
Overvoltage category	II
Insulating material group	I

Automation Technology - Voltage and Power Supply

Product description	7/8" connection cable male cable connector - female cable connector, Contacts: 4, unshielded, moulded cable, IP68, UL, PUR black, 4 x 1.50 mm ² , 10 m
Area	7/8" series 870
Part no.	77 1430 1429 50004-1000

EMC compliance unshielded

Material

Contact body material	PUR
Contact material	CuZn (brass) / CuSn (bronze)
Contact plating	Au (gold)
Locking material	CuZn (brass)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	8d042430-6c6b-4259-84f9-9ebd7cc4adb2

Authorization/approvals

Approvals	UL
-----------	----

Cable data - Structure of the cable

Cable diameter	8.0 mm
Cross section	4 x 1.50 mm ²
Sheath material	PUR
Single-lead insulation	TPM
Single-lead structure	82 x 0.15 mm
Cable color	black

Cable data - Electrical properties

Cable Insulation resistance	> 200 Ω/Km
Operating voltage	600 V
Cable test voltage	4 kV
Conductor resistance	13.3 Ω/Km (20°C)

Cable data - Mechanical properties

Bending radius, fixed cable	≥ 7.5 x Ø
Bending radius, moving cable	≥ 10 x Ø
Bending cycles	5 million
Permitted acceleration	≥ 5 m/s ²
Travel distance, horizontal	20 m
Travel speed	≤ 300 m/min

Cable data - Thermal properties

Temperature range cable in move from/to	-20 °C / 80 °C
Temperature range cable fixed from/to	-50 °C / 80 °C

Automation Technology - Voltage and Power Supply

Product description	7/8" connection cable male cable connector - female cable connector, Contacts: 4, unshielded, moulded cable, IP68, UL, PUR black, 4 x 1.50 mm ² , 10 m
Area	7/8" series 870
Part no.	77 1430 1429 50004-1000

Cable data - Other features

Halogen free	Yes
--------------	-----



Automation Technology - Voltage and Power Supply

Product description	7/8" connection cable male cable connector - female cable connector, Contacts: 4, unshielded, moulded cable, IP68, UL, PUR black, 4 x 1.50 mm ² , 10 m
Area	7/8" series 870
Part no.	77 1430 1429 50004-1000

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP 67 and IP 68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

The plug connector is not suitable for mains voltages Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).