



QU-R-302

OCR-B/ MRZ & PDF417 READER

The QU-R-302 is a hand-held passport and ID cards MRZ reader and bar code reader, it can read OCR-B MRZ ( Machine Readable Zone) from ID card, driver's license, passport; or read 1d and 2d big size PDF417 and QR codes from ID card or driver's license.



### ❖ Read OCR-B/ MRZ From Passport, ID Card

Equipped with Megapixel 1280\*800 high-resolution CMOS image sensor, this enables the QU-R-302 with great performance (quick and accurate) to read the long MRZ ( machine readable zone) in passport and 3 lines MRZ in ID card, driver's license.

### ❖ Read Big Size PDF417 From ID Card

Thanks to its 1280\*800 high resolution sensor, the QU-R-302 is readable those big size and high-density PDF417 code from ID card / driver' license, e.g: IDs of El Salvador, Costa Rica, Colombia, Paraguay, Vietnam, Nicaragua, Panamá, Egypt, South Africa...



<b>Performance</b>	Image Sensor	1280 * 800 CMOS		
	Illumination	White LED		
	Aiming	650nm Laser diode		
	Symbologies	OCR-B/ MRZ	Machine readable passports (MRP) : 2 lines of 44 characters (Readable distance: 15cm-30cm) Travel documents: 3 lines of 30 characters (Readable distance: 14cm-30cm) <b>The best read distance is around 20cm.</b>	
		2D QR PDF417	PDF417in ID documents (Readable distance: 10cm-20cm), QR Code, Data Matrix, AZTEC, CSC, Maxicode, Micro QR, Micro PDF417, GM ,Code One, etc.	
		1D	EAN-13, EAN-8, UPC-A, UPC-E, Code128, Code 39, Codabar, UCC/EAN 128, RSS, ITF, ITF-14, ITF6, Standard25, Matrix 25, COOP 25, Industrial 25, Plessey, MSI Plessey, Code 11,Code 93, Code 49, Code 16K, etc.	
	Resolution	≥3mil (differ from different type bar codes)		
	Typical Depth of Field	EAN-13	70-499mm (13mil)	
		Code 39	90-264mm (5mil)	
		PDF417	70-225mm (6.7mil)	
		Data Matrix	65-214mm (10mil)	
		QR Code	40-294mm (15mil)	
	Scan Mode	Sense mode, Trigger mode		
Scan Angle	Roll: 360°, Pitch: ±61°, Skew:±61°			
Field of View	Horizontal 43°, Vertical 29°			
Min. Symbol Contrast	25%			
<b>Mechanical/ Electric</b>	Interface	RS-232, USB		
	Dimensions	180mm×80mm×90mm		
	Weight	194g		
	Notification	Beep, LED indicator		
	Operating Power	5VDC±5%, 280mA		
<b>Environmental</b>	Operating Temperature	-20°C to 60°C (-4°F to 140°F)		
	Storage Temperature	-40°C to 70°C (-40°F to 158°F)		
	Humidity	5% to 95% (non-condensing)		
<b>Accessories</b>	Cable	USB	USB virtual Com, not support USB-HID	
		RS-232	Standard DB9 RS232 interface	
	Power Adapter	DC5V adapter to power the QU-R-302 for RS-232 interface.		



Tel: +49 202 40 43 29

Website: [www.quio-rfid.de](http://www.quio-rfid.de) Email: [kontakt@quio-rfid.de](mailto:kontakt@quio-rfid.de)

Cronenfelder Straße 75, 42349 Wuppertal Germany